



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: HT706TSAT

Home/Business Theater Surge Suppressor - High-performance surge and line-noise protection for all components



Highlights

- 7 outlets / 6 ft. cord
- 1680 joule rating
- 2-line coaxial surge protection
- 1-line tel/modem surge protection
- \$100,000 [Ultimate Lifetime Insurance](#) (USA and Canada only)

Description

Tripp Lite's HT706TSAT Home/Business Theater Surge Suppressor provides high-performance protection--1680 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 7 outlets (with transformer spacing), 2-line coaxial protection and 1-line tel/modem protection safeguard an entire home/business theater system. \$100,000 [Ultimate Lifetime Insurance](#) coverage (USA and Canada only). Includes two diagnostic LEDs, 6 ft. cord with a right-angle plug, 6 ft. coaxial cable and 6 ft. phone cord.

Applications

Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more

Package Includes

- HT706TSAT Home/Business Theater Surge Suppressor
- 6 ft. coaxial cable
- 6 ft. phone cord
- Instruction manual with warranty information

Features

- 1680 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$100,000 [Ultimate Lifetime Insurance](#) (USA and Canada only) covers connected components against surge damage...for life!
- 7 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 4 transformers
- 2 sets of surge-protected Type F coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line
- 1 set of surge-protected tel/modem connectors (with included 6 ft. phone cord) safeguard personal video recorders (PVRs) on a single dial-up line
- 6 ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Integrated circuit breaker protects against dangerous system

overload
 High-impact plastic housing (black) stands up to the most demanding environments
 UL and CSA listed
 Lifetime product warranty

Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120 VAC
Frequency compatibility	50/60 Hz
OUTPUT	
Output volt amp capacity (amps)	15
Output watts	1800
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Accommodates 4 transformers
INPUT	
Input connection type	NEMA 5-15P
Input cord gauge, type	14 gauge, SJT
Input cord length (ft.)	6 ft.
Input cord length (m)	1.8
Recommended electrical service	120V, 15A
Input plug features	Space-saving right angle input plug
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Built-in LEDs confirm protection and grounding status
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
SURGE / NOISE SUPPRESSION	
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
AC suppression joule rating	1680 joules
Clamping voltage (RMS)	150V
AC suppression response time	< 1 ns
UL1499 let through rating	330V - UL verified
EMI / RFI filtering	Up to 40 dB
PHYSICAL	
Shipping weight (lbs)	5.6
Shipping weight (kg)	2.54
Shipping Dimensions (HWD/in)	2 x 15 x 6
Shipping Dimensions (HWD/cm)	5.1 x 38.1 x 15.2
Unit weight (lbs)	1.2
Unit weight (kg)	0.54
Unit Dimensions (HWD/in)	1.5 x 14 x 2.75
Unit Dimensions (HWD/cm)	3.8 x 35.6 x 7

Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting slots allow desk or wall mounting
AC line cord color	Black
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	CSA
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product warranty	Lifetime
Connected equipment insurance (USA and Canada Only)	\$100,000
DATALINE SURGE SUPPRESSION	
Coax line protection	2 line
Telephone / Modem line protection	1 line
Overview	
Style	Strip

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/products/model.cfm?txtModelID=2810.