



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: HT706TV

### Home/Business Theater Surge Suppressor - High-performance surge and line-noise protection for all components



#### Highlights

- 7 outlets / 6 ft. cord
- 1080 joule rating
- Coaxial surge protection
- \$50,000 [Ultimate Lifetime Insurance](#) (USA and Canada only)

#### Description

Tripp Lite's HT706TV Home/Business Theater Surge Suppressor provides high-performance protection--1080 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 7 outlets (with transformer spacing) and 1-line coaxial protection safeguard an entire home/business theater system. \$50,000 [Ultimate Lifetime Insurance](#) coverage (USA & Canada only). Includes two diagnostic LEDs, 6 ft. cord with a right-angle plug and 6 ft. coaxial cable.

#### Applications

Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more

#### Package Includes

- HT706TV Home/Business Theater Surge Suppressor
- 6 ft. coaxial cable
- Instruction manual with warranty information

#### Features

- 1080 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$50,000 [Ultimate Lifetime Insurance](#) (USA & Canada only) covers connected components against surge damage...for life!
- 7 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely-spaced outlets accommodate up to 4 transformers
- 1 set of Type F surge-protected coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line
- 6 ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status
- Keyhole slots provide convenient wall or cabinet mounting
- Illuminated master switch provides one-touch power control over all components. Integrated circuit breaker protects against dangerous system overload
- High-impact plastic housing (black) stands up to the most demanding environments
- UL and CSA listed

Lifetime product warranty

## Specifications

<b>SYSTEM OVERVIEW</b>	
Voltage compatibility	120 VAC
Frequency compatibility	50/60 Hz
<b>OUTPUT</b>	
Output volt amp capacity (amps)	15
Output watts	1800
Outlet quantity / type	7 NEMA 5-15R
Transformer accommodation	Accommodates 4 transformers
<b>INPUT</b>	
Input connection type	NEMA 5-15P
Input cord gauge, type	14 gauge, SJT
Input cord length (ft.)	6 ft.
Input cord length (m)	1.8
Recommended electrical service	120V, 15A
Input plug features	Space-saving right angle input plug
<b>LEDS ALARMS &amp; SWITCHES</b>	
Diagnostic LEDs	Built-in LEDs confirm protection and grounding status
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
<b>SURGE / NOISE SUPPRESSION</b>	
Protection modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
AC suppression joule rating	1080 joules
Clamping voltage (RMS)	150V
AC suppression response time	< 1 ns
UL1499 let through rating	330V - UL verified
EMI / RFI filtering	Up to 40 dB
<b>PHYSICAL</b>	
Shipping weight (lbs)	5.02
Shipping weight (kg)	2.28
Shipping Dimensions (HWD/in)	2 x 15 x 6
Shipping Dimensions (HWD/cm)	5.1 x 38.1 x 15.2
Unit weight (lbs)	1
Unit weight (kg)	0.45
Unit Dimensions (HWD/in)	1.5 x 14 x 2.75
Unit Dimensions (HWD/cm)	3.8 x 35.6 x 7
Material of construction	Plastic
Integrated keyhole mounting tabs	Keyhole mounting slots allow desk or wall mounting

AC line cord color	Black
<b>CERTIFICATIONS</b>	
UL1449 1998 Rev. (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
cUL / CSA (Canada)	CSA
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product warranty	Lifetime
Connected equipment insurance (USA and Canada Only)	\$50,000
<b>DATALINE SURGE SUPPRESSION</b>	
Coax line protection	1 line
<b>Overview</b>	
Style	Strip

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/products/model.cfm?txtModelID=2811](http://www.tripplite.com/products/model.cfm?txtModelID=2811).