



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDUMV15

Metered PDU / Power Distribution Unit - Safe, reliable power distribution with digital current meter

Highlights

- Digital current meter display
- 16 outlets
- Convenient and safe covered on/off switch
- 15 amp breaker
- 15-ft. cord
- 48" length



Description

Tripp Lite's PDUMV15 metered power distribution unit offers 15 amp, 120V multi-outlet AC power distribution in a convenient 48-inch mountable housing. Digital current meter displays the power consumption of connected equipment. Offers vertical power distribution in rackmount, raceway, and workbench applications. Includes 16 NEMA 5-15R output receptacles, 15 ft. AC line cord, and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal extruded aluminum housing stands up to demanding network, laboratory, or factory environments. Unfiltered electrical pass-through makes the PDUMV15 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Included 16 NEMA5-15R outlets, 15-ft. AC power cord with 5-15P plug, 15 amp circuit breaker in rugged metal case design.

PLUG/OUTLETS-Input: NEMA 5-15P/Output: 16 NEMA 5-15R

ELECTRICAL - 120V AC, 50/60Hz, 15A

FORMAT - 48 inch mountable strip format

Applications

Ideal for horizontal or vertical raceway style metered power distribution in office, workbench, industrial, networking, and telecom applications.

Package Includes

- PDUMV15 Metered Vertical PDU
- Mounting hardware
- 6 outlet safety covers
- Owner's manual with warranty information

Features

- Digital current monitoring display
- Sturdy all-metal 48-inch corded PDU
- Includes hardware for Zero U configuration in rack enclosures as well as horizontal mounting in raceways and more
- 16 NEMA 5-15R output receptacles
- Lighted power switch with locking transparent safety cover prevent accidental shutoff of connected devices
- 15 amp electrical capacity with circuit breaker

120V, 50 /60Hz electrical compatibility
 15 ft. power cord
 Lifetime warranty

Specifications

SYSTEM OVERVIEW	
Voltage compatibility	120V
Frequency compatibility	50 / 60Hz
OUTPUT	
Output VA	15A / 1800VA
Output nominal voltage	120V
Outlet quantity / type	16 NEMA 5-15R
Overload protection	15A
INPUT	
Maximum input amps	15A
Input connection type	NEMA 5-15P
Input cord length	15 ft.
LEDS ALARMS & SWITCHES	
Front panel LEDs	Digital LED current monitor display
Switches	Lighted on/off switch with integrated safety cover
PHYSICAL	
Shipping weight (lbs)	4.2
Shipping Dimensions (HWD/in)	51.5 x 3.5 x 2.5
Unit weight (lbs)	3.8
Unit Dimensions (HWD/in)	3 x 48 x 1.5
Material of construction	Aluminum
Form factors supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
WARRANTY	
Product warranty	Lifetime warranty
SPECIAL FEATURES	
Appearance	Silver housing

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/products/model.cfm?txtModelID=3458.