



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: PDUV15

**Safe, reliable power distribution for critical networking equipment**

### Highlights

- 12 outlets
- Convenient and safe covered on/off switch
- Integrated button mounts
- 15-amp breaker
- 15-ft. cord
- 36" length



### Description

Tripp Lite's PDUV15 Basic Vertical Power Distribution Unit offers 15-amp, 120V multi-outlet AC power distribution in a convenient 36-inch mountable housing. It offers vertical power distribution in rackmount, raceway and workbench applications. Includes 12 NEMA 5-15R output receptacles, 15-ft. AC line cord and lighted power switch with locking transparent cover to prevent accidental shutoff. Sturdy all-metal aluminum housing stands up to demanding network, laboratory or factory environments. Unfiltered electrical pass-through makes the PDUV15 ideal for distributing alternate waveform UPS or generator power in rack enclosures, network closets and more. Included 12 NEMA5-15R outlets, 15-ft. AC power cord with 5-15P plug, 15-amp circuit breaker in rugged metal case design with universal and button mounting options. PLUG/OUTLETS - Input: NEMA 5-15P; Output: 12 NEMA 5-15R; ELECTRICAL - 120V AC, 50/60Hz, 15A; FORMAT - 36-inch mountable strip.

### Applications

Ideal for horizontal or vertical raceway-style power distribution in office, workbench, industrial, networking and telecom applications.

### Package Includes

- PDUV15 Basic Vertical PDU
- Mounting hardware
- Owner's manual with warranty information

### Features

- Sturdy all-metal, 36-inch corded PDU
- Includes integrated button mount and hardware for 0U configuration in rack enclosures as well as horizontal mounting in raceways and more
- 12 NEMA 5-15R output receptacles
- Lighted power switch with locking transparent safety cover prevent accidental shutoff of connected device
- 15-amp electrical capacity with circuit breaker
- 120V, 50/60Hz electrical compatibility
- 15-ft. power cord
- Lifetime warranty

## Specifications

<b>SYSTEM OVERVIEW</b>	
Voltage compatibility	120V
Frequency compatibility	50/60Hz
<b>OUTPUT</b>	
Output VA	15A/1800VA
Output nominal voltage	120V
Outlet quantity / type	12 NEMA 5-15R
Overload protection	15A
<b>INPUT</b>	
Maximum input amps	15A
Input connection type	NEMA 5-15P
Input cord length	15-ft.
<b>LEDS ALARMS &amp; SWITCHES</b>	
Switches	Lighted on/off switch with integrated safety cover
<b>PHYSICAL</b>	
Shipping weight (lbs)	3.8
Shipping Dimensions (HWD/in)	3 x 40 x 2.75
Unit weight (lbs)	3.3
Unit Dimensions (HWD/in)	1.75 x 36 x 1.25
Material of construction	Aluminum
Form factors supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
<b>WARRANTY</b>	
Product warranty	Lifetime warranty
<b>SPECIAL FEATURES</b>	
Appearance	Black housing

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/products/model.cfm?txtModelID=3880](http://www.tripplite.com/products/model.cfm?txtModelID=3880).