

Protect It!™ Safety Series Surge Suppressors



- ▶ Up to 3600 Joules
- ▶ Up to \$100,000 Insurance
- ▶ Up to 8 AC Outlets
- ▶ Up to 25 ft. Power Cord
- ▶ All-Metal Housing
- ▶ OSHA Yellow Color

Provide Industrial-Strength Protection

Protect It! Safety Series Surge Suppressors provide industrial-strength surge and line-noise protection for a variety of tools and appliances: drills, saws, sanders, compressors, chargers, pumps and more. Premium features and rugged all-metal housings make these models ideal for every workshop, garage, laboratory, industrial facility and construction site. High-visibility OSHA yellow color alerts user and others that power cords and tools are in use.


Deliver Premium Features & Insurance

Protect It! Safety Series Surge Suppressors provide the highest UL-verified joule ratings of any surge suppressors in their class. Joule ratings measure a surge suppressor's ability to handle surges; more joules mean more protection. In addition, all models filter disruptive EMI/RFI line noise to improve the performance of connected equipment. Up to \$100,000 Ultimate Lifetime Insurance guarantees equipment will stay safe from surge damage, including direct lightning strikes, for life. All models are backed by a lifetime limited warranty.

Feature Focus



"Protected" LED
Confirms that surge suppression components are protecting connected equipment.



Outlet Safety Covers
Shield unused outlets from debris and accidental contact.



Optional Wallmount
Integrated keyhole slots on bottom panel provide convenient wall or bench mounting.



Illuminated ON/OFF Switch with Integrated Circuit Breaker
Provides power control over connected equipment. Breaker guards against dangerous system overload.



Rugged All-Metal Housing
Stands up to the harshest environments.



Transformer Outlets
Accommodate multiple transformers without blocking other outlets.



Cord Wrap with Hang Holes
Provides convenient cord management.

Specifications



| Model # | Outlets | Joules | Transformer Outlets | Diagnostic LED | Outlet Safety Covers | Cord Length (ft.) | Cord Wrap with Hang Holes | Integrated Cord Clip | Ultimate Lifetime Insurance* | Housing Style** |
|----------|---------|--------|---------------------|----------------|----------------------|-------------------|---------------------------|----------------------|------------------------------|-----------------|
| TLM825SA | 8 | 3600 | 3 | Protected | 4 | 25 | Yes | Yes | \$100,000 | A |
| TLM812SA | 8 | 1200 | 3 | Protected | 4 | 12 | Yes | Yes | \$50,000 | A |
| TLM615SA | 6 | 2400 | 2 | Protected | 4 | 15 | Yes | Yes | \$75,000 | B |
| TLM609SA | 6 | 1200 | 2 | Protected | 4 | 9 | Yes | Yes | \$50,000 | B |
| TLM626SA | 6 | 420 | 2 | Protected | 4 | 6 | — | — | \$10,000 | C |

OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. These Tripp Lite products comply with those guidelines. All models are rated to 120V AC (50/60 Hz) operation. All outlets are NEMA 5-15R. All plugs are grounded, straight-blade NEMA 5-15P * Ultimate Lifetime Insurance is valid in the U.S., Puerto Rico and Canada. ** Photos represent housing style only. Refer to specification chart for exact model features. The policy of Tripp Lite is one of continuous improvement. Specifications are subject to change without notice. Actual products may differ from photos.

Complete specifications available at www.tripplite.com

Power It!™ Safety Series Power Strips



- ▶ Up to 8 AC Outlets
- ▶ Up to 25 ft. Power Cord
- ▶ GFCI Plug Options
- ▶ All-Metal Housing
- ▶ OSHA Yellow Color

Provide Safe, Dependable Power

Power It! Safety Series Power Strips provide a reliable source of AC power for a variety of tools and appliances: drills, saws, sanders, compressors, chargers, pumps and more. Premium features and rugged construction make these models ideal for every workshop, garage, laboratory, industrial facility and construction site. High-visibility OSHA yellow color alerts user and others that power cords and tools are in use.

Deliver Premium Features

Protect It! Safety Series Power Strips combine all of the premium features found separately in competitive models into one versatile power strip series. All models feature all-metal housings that stand up to the most demanding environments. In addition, all models are backed by a lifetime limited warranty. Select models feature a GFCI plug with a resettable breaker.

Feature Focus



GFCI Plug (Select Models)

Protects users from electrical shock in wet or humid environments.



Illuminated ON/OFF Switch with Integrated Circuit Breaker

Provides power control over connected equipment. Breaker guards against overload.



Outlet Safety Covers

Shield unused outlets from debris and accidental contact.



Rugged All-Metal Housing

Stands up to the harshest environments.



Cord Wrap with Hang Holes

Provides convenient cord management.



Optional Wallmount

Integrated keyhole slots on bottom panel provide convenient wall or bench mounting.



Transformer Outlets

Accommodate multiple transformers without blocking other outlets.

Specifications



| UL US | Outlets | Transformer Outlets | Outlet Safety Covers | Cord Length (ft.) | Cord Wrap with Hang Holes | Integrated Cord Clip | Housing Style |
|--|---------|---------------------|----------------------|-------------------|---------------------------|----------------------|---------------|
| Power It! Safety Series Power Strips—WITH GFCI PLUG | | | | | | | |
| TLM825GF | 8 | 3 | 4 | 25 | Yes | Yes | A |
| TLM812GF | 8 | 3 | 4 | 12 | Yes | Yes | A |
| TLM609GF | 6 | 2 | 4 | 9 | Yes | Yes | B |
| Power It! Safety Series Power Strips | | | | | | | |
| TLM815NS | 8 | 3 | 4 | 15 | Yes | Yes | A |
| TLM609NS | 6 | 2 | 4 | 9 | Yes | Yes | B |
| TLM626NS | 6 | 2 | 4 | 6 | — | — | C |

OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. These Tripp Lite products comply with those guidelines. All models are rated to 120V AC (50/60 Hz) operation. All outlets are NEMA 5-15R. All plugs are grounded, straight-blade NEMA 5-15P. * Photos represent housing style only. Refer to specification chart for exact model features. The policy of Tripp Lite is one of continuous improvement. Specifications are subject to change without notice. Actual products may differ from photos.

Complete specifications available at www.tripplite.com



Tripp Lite World Headquarters • 1111 W. 35th Street, Chicago, IL 60609
www.tripplite.com • (773) 869-1234