


LEFT SIDE VIEW



FRONT VIEW  
DOOR REMOVED

3 BREAKER MAINTENANCE BYPASS PANEL (MBP)				
PART NUMBER	BREAKER TYPE	BREAKER FRAME	BREAKER TRIP	A. I. C. RATING
SU20KMBP	EHD	100 AMP	80	208/120V 18,000
SU30KMBP	ED	225 AMP	125	" 65,000

PANEL TYPE: CDP (UL 67 LISTED INTERIOR)  
 SERVICE: SEE TABLE ABOVE.  
 ENCLOSURE: NEMA 1 (UL 50 LISTED ENCLOSURE)  
 BOX: 12 GAUGE PAINTED STEEL, NO KNOCKOUTS.  
 TRIM: 12 GAUGE PAINTED STEEL, HELD TO BOX WITH ADJUSTABLE TRIM CLAMPS - SURFACE MOUNTING.  
 DOOR: EQUIPPED WITH CORBIN 15767 SNAPLOCK.  
 FINISH: BEIGE POLYESTER POWDERCOAT APPLIED TO SURFACES TREATED WITH AN IRON PHOSPHATE AND CHROME FREE SEALER.  
 BUS: ELECTROLYTIC COPPER OF 98% CONDUCTIVITY, BASED ON 1000 AMPS PER SQUARE INCH DENSITY.  
 WIRE BENDING GUTTER: MEETS OR EXCEEDS NEC TABLES 373-6(a), 373-6(b).  
 BREAKERS: CUTLER-HAMMER THERMAL-MAGNETIC, 3 POLE, TRIP AND FRAME AS INDICATED:  
 SEE TABLE ABOVE FOR BREAKER TYPE, AMPERES, AND A. I. C. RATING.  
 BREAKER TERMINAL LUG: 15 - 100 AMP (1) #14-1/0 PER PHASE. 101 - 225 AMP (1) #4-4/0 PER PHASE.

