

## Industrial Power Strip, 3-Outlet, 9 ft. (2.7 m) Cord, NEMA 5-15P Plug, Switch Guard

MODEL NUMBER: 3SP9



Durable all-metal industrial power strip distributes power to appliances, power tools, lights and other heavy-duty electrical equipment in industrial and commercial settings.

### Description

The 3SP9 3-Outlet Industrial Power Strip is the perfect power distribution solution for appliances, power tools, lighting and other electrical equipment in both industrial and commercial settings. Its rugged all-metal housing is designed for demanding environments, making it ideal for a factory floor, warehouse, server room or commercial space. Keyhole mounting tabs let you install the 3SP9 wherever convenient—on a wall, floor, workbench or under a counter.

Three NEMA 5-15R outlets are arranged in standard 1.75-inch center-to-center spacing for easy connection to equipment. A built-in unfiltered electrical pass through makes the 3SP9 ideal for distributing alternate waveform power from a UPS system or generator to connected equipment. The long nine-foot (2.7-meter) power cord with NEMA 5-15P plug lets the 3SP9 be mounted away from the power source for maximum convenience and flexibility.

A built-in 15A circuit breaker detects dangerous overloads that could damage valuable equipment and immediately shuts down the 3SP9. A transparent switch cover protects against accidental shutdowns. A lighted on/off switch confirms at a glance that the power strip is operating.

### Features

#### Perfect Worksite Power Distribution

- Ideal for powering appliances, power tools, lighting and other electrical equipment
- 3 NEMA 5-15R outlets with 1.75 in. center-to-center spacing
- 9-ft. (2.74 m) power cord with NEMA 5-15P plug
- Meets UL1363 (USA) and cUL (Canada) certifications

#### Premium Safety Features

- 15A resettable circuit breaker prevents dangerous overloads
- Transparent switch cover eliminates accidental shutdowns
- Lighted on/off switch confirms operation at a glance

#### Unfiltered Electrical Pass Through

- Distributes alternate waveform power from UPS system or generator to connected equipment

### Highlights

- 3 NEMA 5-15R outlets with 1.75 in. center-to-center spacing
- 15A resettable circuit breaker
- Lighted on/off switch with transparent safety cover
- Heavy-duty all-metal housing
- 9-ft. (2.74 m) power cord with NEMA 5-15P plug

### Package Includes

- 3SP9 3-Outlet Industrial Power Strip, 9 ft. (2.7 m) Cord
- Owner's manual

**Heavy-Duty All-Metal Housing**

- Designed for demanding environments, such as factories, warehouses, server rooms and commercial spaces
- 8.6 in. length for minimal footprint
- Keyhole mounting tabs for installation on a wall, floor, workbench or under a counter

## Specifications

OVERVIEW	
UPC Code	037332189653
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	9
Right-Angle Plug	No
Input Cord Length (m)	2.74
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(1) Yes
Outlet Orientation	Single row of 3
Right-Angle Outlets	No
Outlet Spacing	1.75 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent locking switch cover prevents accidental shutoff
PHYSICAL	
Color	Gray
Material of Construction	Metal
Power Cord Color	Black
Mounting Holes or Slots	Yes



Powering Business Worldwide



Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 5.70 x 10.20
Shipping Dimensions (hwd / cm)	6.10 x 14.48 x 25.91
Shipping Weight (lbs.)	1.90
Shipping Weight (kg)	0.86
Unit Dimensions (hwd / in.)	1.500 x 8.750 x 2.500
Unit Dimensions (hwd / cm)	3.81 x 22.2 x 6.35
Outlet Spacing	1.75 in.
Mounting Details	Includes flanges
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Built-In Circuit Breaker	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
 Cleveland, OH 44122  
 United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
 Eaton is a registered trademark. All other trademarks  
 are the property of their respective owners.