

Multi-Device Charging Station, 16 USB Ports, iPad and Android Tablets, Wall-Mount Option Black

MODEL NUMBER: **CS16USB**



Locking steel cabinet provides 2.4A USB charging, syncing, secure storage and cord management for up to 16 tablets and other USB devices. Recommended for education, office, commercial, retail, industrial and healthcare environments.

Features

Fast Charging

- 16 USB ports provide fastest charging supported by each device, up to 2.4A per port
- Recommended for iPad®, Android™, Surface™ and Kindle™ tablets
- Also charges mobile phones and other USB devices
- Detachable 10-ft. (3.05 m) AC input cord with NEMA 5-15P plug

Convenient Syncing

- USB sync uplink port connects to host computer for wired syncing
- Compatible with wireless syncing
- Supports simultaneous syncing and charging (up to 1.5A per port during wired syncing)

Comprehensive Protection

- Sturdy steel construction and powder-coated finish promote long-term durability
- Doors lock with included keys to help prevent device theft, damage or tampering
- Flow-through ventilation helps prevent devices from overheating
- Coated shelf shields devices from scratches and scuffs

Flexible Configuration

- Ships fully assembled
- Supports mounting to wall, desk, table, counter or floor
- Door opens 180 degrees for improved device and service access
- Removable dividers accommodate thicker devices
- Firmware upgrade port for future updates

Highlights

- Fast 2.4A USB charging, syncing and storage for 16 devices
- Locking steel cabinet with flow-through ventilation
- Adjustable device dividers and integrated cord management
- Ships fully assembled and mounts to wall, desk, table or floor
- Detachable 10-ft. (3.05 m) power cord

Package Includes

- CS16USB 16-Device USB Charging Station Cabinet, Black
- Detachable 10-ft. (3.05 m) AC input cord w/NEMA 5-15P plug
- (2) Keys
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332185419
Product Type	Multi-Device Charger
Charging Form Factor	Stationary Cabinet
Charger Functions	Charge; Secure; Sync
Device Compatibility	Tablet; Phone
Device Slots	16
INPUT	
Nominal Input Voltage(s) Supported	120V AC; 230V AC
Voltage Compatibility (VAC)	110-240
Input Frequency	50 / 60 Hz (auto-select)
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
POWER	
Power Consumption (Watts)	56
CHARGING	
Number of Charging Ports	16
Total Charging Amps	40A
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	Pass through
Charging Ports / Amps	(16) 2.4A
Overcharge Protection	Yes
Charging Amps per Port	2.4A
PHYSICAL	
Color	Black
Material of Construction	Steel
Charging Station Form Factor	Stationary Cabinet
Shipping Dimensions (hwd / in.)	18.20 x 21.20 x 26.80

Shipping Dimensions (hwd / cm)	46.23 x 53.85 x 68.07
Shipping Weight (lbs.)	62.00
Shipping Weight (kg)	28.12
Slot Dimensions (hwd / in.)	8,1 x 0,8 x 13,9
Slot Dimensions (hwd / mm)	206 x 20,1 x 353,8
Unit Dimensions (hwd / in.)	14.570 x 23.620 x 17.720
Unit Dimensions (hwd / cm)	37,01 x 59,99 x 45,01
Unit Weight (lbs.)	55.14
Unit Weight (kg)	25.01
Number of Shelves	1
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
Cord Management	Yes
Overcurrent Protection	Yes
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	Yes
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Locking	Yes
Lock Type	Key
STANDARDS & COMPLIANCE	
Product Certifications	NOM (Mexico); UL 60950-1
Product Compliance	RoHS; CE (Europe); EIA/ECA-310-E; REACH; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.