

Full Motion Universal Tablet Desk Clamp

MODEL NUMBER: **DDR1013SC**



Highlights

- Increases valuable workspace on your desk, table or workstation
- Fits tablets ranging from 10 in. to 13.5 in.
- Adjusts display angle and height with just a touch
- Rotates 360°
- Supports up to 3.1 lbs (1.4 kgs)

Package Includes

- DDR1013SC Full-Motion Universal Tablet Desk Clamp
- Owner's Manual

Mount your tablet off the surface of your desk, table or workstation to free up valuable space. Customize the tablet's angle and height to fit your environment and comfort level.

Description

The DDR1013SC Full-Motion Universal Tablet Desk Clamp attaches to your desk, table or workstation, allowing you to mount your tablet above it and free up valuable workspace. The mount clamps firmly to most flat surfaces up to 2.75 in. thick, and the 23-inch flexible arm lets you adjust your tablet's angle and height to fit your environment and comfort level. Two separate holders fit tablets ranging from 10 inches to 13.5 inches. Both rotate 360°, so you can view your tablet in portrait and landscape modes. The sleekly designed DDR1013SC comes preassembled for easy installation in seconds with no tools necessary. Supports weights up to 3.1 lbs (1.4 kgs)

Features

Attaches to Almost Any Desk, Table or Workstation

- Durable, sturdy clamp fits tightly to most flat surfaces up to 2.75 in. thick
- Flexible 23-inch arm lets you adjust height and angle for perfect viewing
- Full 360° rotation for both portrait and landscape modes

Installs in Seconds

- Comes preassembled for easy installation—no tools necessary
- Included holders fit most tablets from 10 in. to 13.5 in.
- Supports up to 3.1 lbs (1.4 kgs)

Specifications

OVERVIEW	
UPC Code	037332186539



Powering Business Worldwide



Device Compatibility	Tablet
PHYSICAL	
Color	Black
Material of Construction	Steel
Motion	Full
Mounting Location	Desk Clamp
Degrees of Motion	360 Rotate
Minimum Screen Size (in.)	10
Minimum Screen Size (cm)	25.4
Maximum Screen Size (in.)	13.5
Maximum Screen Size (cm)	34.29
Maximum Weight Capacity (lbs.)	3.1
Maximum Weight Capacity (kg)	1
Shipping Dimensions (hwd / in.)	2.90 x 3.10 x 31.30
Shipping Dimensions (hwd / cm)	7.37 x 7.87 x 79.50
Shipping Weight (lbs.)	5.50
Shipping Weight (kg)	2.49
Unit Dimensions (hwd / in.)	23.400 x 2.200 x 2.070
Unit Dimensions (hwd / cm)	59.4 x 5.59 x 5.26
Unit Weight (lbs.)	2.6
Unit Weight (kg)	1.18
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	No
Security Lock	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.