



Fixed Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DWF1323M











Highlights

- SEE NEW MODEL -DWF1327M
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 13" to 27"
- Supports up to 88 lbs.
- 5-year warranty

Package Includes

- DWF1323M Fixed Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Description

Tripp Lite's VESA-compliant DWF1323M Fixed Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance. Its durable, all-metal frame with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays. It comes pre-assembled for quick and easy installation. For peace of mind, the DWF1323M comes backed by a 5-year warranty.

Features

- VESA-compliant DWF1323M Fixed Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance
- Durable, all-metal frame with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays
- Pre-assembled for quick and easy installation
- 5-year warranty

Specifications

| OVERVIEW | | |
|--------------------------|-----------------------|--|
| UPC Code | 037332178732 | |
| | | |
| PHYSICAL | | |
| Color | Black | |
| Material of Construction | Metal | |
| VESA Pattern (mm) | 50x50; 75x75; 100x100 | |
| Motion | Fixed | |





| Mounting Location | Wall | |
|---|-------------------------|--|
| Degrees of Motion | Fixed | |
| Maximum Weight Capacity (lbs.) | 88 | |
| Maximum Weight Capacity (kg) | 40 | |
| Shipping Dimensions (hwd / in.) | 5.71 x 5.31 x 0.79 | |
| Shipping Dimensions (hwd / cm) | 14.50 x 13.49 x 2.01 | |
| Shipping Weight (lbs.) | 1.43 | |
| Shipping Weight (kg) | 0.65 | |
| Unit Dimensions (hwd / in.) | 4.720 x 5.500 x 0.600 | |
| Unit Weight (lbs.) | 1.43 | |
| Unit Weight (kg) | 0.65 | |
| FEATURES & SPECIFICATIONS | | |
| Cord Management | No | |
| Tools Necessary | Yes | |
| WARRANTY & SUPPORT | | |
| Product Warranty Period (Worldwide) | 5-year limited warranty | |
| Product Warranty Period (U.S. & Canada) | 5-year limited warranty | |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.