

# Full-Motion Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DWM1323SE



## Description

Tripp Lite's VESA-compliant DWM1323SE Tilt Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly re-position your display at any time, even after installation. Its sleek design features convenient one-touch swivel display adjustment with tilt capabilities and fits most 13- to 27-inch flat-panel displays. Its durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 33 lb. For peace of mind, the DWM1323SE comes backed by a 5-year warranty and green, RoHS-compliant design.

## Features

- Tripp Lite's VESA-compliant DWM1323SE Tilt Flat-Screen Wall Mount offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly re-position your display at any time, even after installation
- Sleek design features convenient one-touch swivel display adjustment with tilt capabilities
- Fits most 13- to 27-inch flat-panel displays
- Durable, all-metal frame with scratch-resistant, powder-coat finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware and supports weights of up to 33 lb
- 5-year warranty
- Green, RoHS-compliant design

## Specifications

OVERVIEW	
UPC Code	037332178794
PHYSICAL	

## Highlights

- SEE NEW MODEL - DWM1327SE
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 13" to 27"
- Convenient one-touch swivel display adjustment for easy view optimization (tilt is adjustable with included Allen wrench)
- Wide range of motion with -15° to +15° tilt and 180° swivel capability
- Supports up to 33 lbs.
- 5-year warranty

## Package Includes

- DWM1323SE Full Motion Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual



Powering Business Worldwide



Color	Black
Material of Construction	Metal
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 180 Swivel
Maximum Weight Capacity (lbs.)	33
Maximum Weight Capacity (kg)	15
Min/Max Arm Extension (in.)	4.14 min to 15.95 max
Min/Max Arm Extension (cm)	10.5 min to 40 max
Shipping Dimensions (hwd / in.)	11.02 x 9.45 x 2.83
Shipping Dimensions (hwd / cm)	27.99 x 24.00 x 7.19
Shipping Weight (lbs.)	2.70
Shipping Weight (kg)	1.22
Unit Dimensions (hwd / in.)	8.260 x 4.600 x 16.000
Unit Weight (lbs.)	2.66
Unit Weight (kg)	1.21
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.