

Full-Motion Wall-Mount for 17" to 42" Flat-Screen Displays

MODEL NUMBER: DWM1737MN



Description

Tripp Lite's VESA-compliant DWM1737MN Full-Motion Flat-Screen Wall Mount packs a lot of functionality into a compact design. It offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its low-profile frame features convenient one-touch display adjustment with tilt and swivel capabilities and fits most 17- to 42-inch flat-panel displays. Its durable, all-metal construction with scratch-resistant, powder-coat finish withstands the stress of repeated use. It comes preassembled for quick and easy installation and supports weights of up to 115 lbs. For peace of mind, the DWM1737MN comes backed by a 5-year warranty.

Features

- Tripp Lite's VESA-compliant DWM1737MN Full-Motion Flat-Screen Wall Mount packs a lot of functionality into a compact design
- Offers full-motion articulation and can free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation
- Low-profile frame features convenient one-touch display adjustment with tilt and swivel capabilities
- Fits most 17- to 42-inch flat-panel displays
- Durable, all-metal construction with scratch-resistant, powder-coat finish withstands the stress of repeated use
- Comes preassembled for quick and easy installation
- supports weights of up to 115 lb
- 5-year warranty

Highlights

- SEE NEW MODEL - DWM1742MN
- Can be used to increase available desk/table space in office applications
- Fits most flat-panel displays from 17" to 42"
- Convenient one-touch display adjustment for easy view optimization
- Wide range of motion with -15° to +15° tilt, 80° swivel and -4° to +4° screen level adjustment capability
- Supports up to 115 lbs.
- 5-year warranty

Package Includes

- DWM1737MN Full-Motion Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332178725



Powering Business Worldwide



PHYSICAL	
Color	Black
Material of Construction	Metal
VESA Pattern (mm)	75x75; 100x100; 200x100; 200x200
Motion	Full
Mounting Location	Wall
Degrees of Motion	-15/+15 Tilt; 80 Swivel; -4/+4 Level Adjustment
Maximum Weight Capacity (lbs.)	115
Maximum Weight Capacity (kg)	52
Shipping Dimensions (hwd / in.)	3.54 x 9.06 x 9.45
Shipping Dimensions (hwd / cm)	8.99 x 23.01 x 24.00
Shipping Weight (lbs.)	3.60
Shipping Weight (kg)	1.63
Unit Dimensions (hwd / in.)	7.870 x 2.200 x 1.280
Unit Weight (lbs.)	3.63
Unit Weight (kg)	1.65
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.