

Tilt Wall-Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: DWT1323S



Description

Tripp Lite's VESA-compliant DWT1323S Tilt Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance. With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into a compact frame. It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 88 lbs. and fits most 13- to 27-inch flat-panel displays. It comes preassembled for quick and easy installation and features horizontal adjustment to compensate for off-center wall studs. For peace of mind, the DWT1323S comes backed by a 5-year warranty and green, RoHS-compliant design.

Features

- Tripp Lite's VESA-compliant DWT1323S Tilt Flat-Screen Wall Mount's low-profile design stays hidden behind your display for a sleek, professional appearance
- Tilt adjustment improves viewing angles in applications where the audience is located below the display
- It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation
- Durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 88 lb
- Fits most 13- to 27-inch flat-panel displays
- It comes preassembled for quick and easy installation and features horizontal adjustment to compensate for off-center wall studs
- 5-year warranty
- Green, RoHS-compliant design

Specifications

OVERVIEW

Highlights

- **SEE NEW MODEL - DWT1327S**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 13" to 27"
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -15° to +10° tilt capability
- Supports up to 88 lbs.
- 5-year warranty

Package Includes

- DWT1323S Tilt Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual



Powering Business Worldwide



UPC Code	037332178749
PHYSICAL	
Color	Black
Material of Construction	Metal
VESA Pattern (mm)	75x75; 100x100
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-15/+10 Tilt
Maximum Weight Capacity (lbs.)	88
Maximum Weight Capacity (kg)	40
Shipping Dimensions (hwd / in.)	1.57 x 4.92 x 5.12
Shipping Dimensions (hwd / cm)	3.99 x 12.50 x 13.00
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
Unit Dimensions (hwd / in.)	4.720 x 7.720 x 1.600
Unit Weight (lbs.)	1.01
Unit Weight (kg)	0.46
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.