


Tilt Wallmount for 26" to 55" Flat-Screen Displays

MODEL NUMBER: DWT2647XP



Description

Tripp Lite's VESA-compliant DWT2647XP Tilt Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility. With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into an unobtrusive frame. It can also free up valuable space in your workstation by allowing you to effortlessly reposition your display at any time, even after installation. Its durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lbs. and fits most 26- to 55-inch flat-panel displays. It comes with all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs. A built-in bubble level enables accurate display leveling. For peace of mind, the DWT2647XP comes backed by a 5-year warranty and green, RoHS-compliant design.

Features

- Tripp Lite's VESA-compliant DWT2647XP Tilt Flat-Screen Wall Mount's low-profile design features an open frame for easy wall access and optimal display positioning flexibility
- With tilt adjustment for improved viewing angles in applications where the audience is located below the display, it packs a lot of functionality into an unobtrusive frame
- Free up valuable space in your workstation by effortlessly repositioning your display at any time, even after installation
- Durable, all-metal construction with scratch-resistant, powder-coat finish supports weights of up to 165 lb
- Fits most 26- to 55-inch flat-panel displays
- Comes with all necessary mounting hardware and features horizontal adjustment to compensate for off-center wall studs
- Built-in bubble level enables accurate display leveling
- 5-year warranty
- Green, RoHS-compliant design

Highlights

- **SEE NEW MODEL - DWT2655XP**
- Low-profile mounting keeps unit out of sight for sleek, professional appearance
- Fits most flat-panel displays from 26" to 55"
- Open frame for easy wall access
- Tilt adjustment improves viewing angles in applications where the audience is below the display
- Horizontal adjustment compensates for off-center wall studs
- Wide range of motion with -10° to +10° tilt capability
- Equipped with a bubble level for accurate display leveling
- Supports up to 165 lbs.
- 5-year warranty

Package Includes

- DWT2647XP Tilt Flat-Screen Wall Mount
- Mounting Hardware
- Owner's Manual



Powering Business Worldwide



Specifications

OVERVIEW	
UPC Code	037332178800
PHYSICAL	
Color	Black
Material of Construction	Metal
VESA Pattern (mm)	100x100; 200x100; 200x200; 400x200; 400x400
Motion	Tilt
Mounting Location	Wall
Degrees of Motion	-10/+10 Tilt
Maximum Weight Capacity (lbs.)	165
Maximum Weight Capacity (kg)	75
Shipping Dimensions (hwd / in.)	19.29 x 6.30 x 1.97
Shipping Dimensions (hwd / cm)	49.00 x 16.00 x 5.00
Shipping Weight (lbs.)	6.78
Shipping Weight (kg)	3.08
Unit Dimensions (hwd / in.)	17.320 x 18.100 x 2.500
Unit Weight (lbs.)	6.78
Unit Weight (kg)	3.08
FEATURES & SPECIFICATIONS	
Cord Management	No
Tools Necessary	Yes
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty
Product Warranty Period (U.S. & Canada)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.