

Universal Monitor Riser, Height-Adjustable, Black

MODEL NUMBER: MR1612



Raises your monitor incrementally up to 5.25 inches above your desk, table or workspace's surface to help ease eye and neck strain and free up valuable space. Ideal for laptops, monitors or printers.

Description

The MR1612 Universal Monitor Riser frees up valuable space on your desk, table or workstation by placing your monitor from 1.25 to 5.25 inches above the surface. Use the included short and long leg segments to create a height that's comfortable for you. Ideal for home or office, the MR1612 helps ease eye and neck strain. You can also use it for laptops and printers. The riser's extra-large 15.5 x 11.25 inch platform supports up to 40 pounds. Rubber feet secure the riser in place on smooth surfaces. Assembles in just a few seconds.

Features

Ideal for Monitors, Laptops or Printers

- Raises monitor in increments 1.25 to 5.25 in. above desk surface
- Frees up valuable work space
- Helps ease strain on eyes and neck
- For home or office

Durable Construction

- Extra-large 15.5 x 11.25 in. platform supports up to 40 lb.
- Rubber feet secure riser in place on smooth surfaces
- Assembles easily in seconds

Highlights

- Included leg segments raise monitor in increments
- Extra-large 15.5 x 11.25 in. platform securely holds riser in place
- Rubber feet prevent unit from sliding on smooth surfaces
- Supports up to 40 lb.
- Assembles in seconds

Package Includes

- Riser platform
- (4) Long legs, 2 in.
- (8) Short legs, 1.25 in.
- (4) Rubber feet, .13 in.
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332191724
Device Compatibility	Monitor/HDTV
PHYSICAL	



Powering Business Worldwide



Color	Black
Material of Construction	Plastic
Mounting Location	Desktop
Maximum Weight Capacity (lbs.)	40
Maximum Weight Capacity (kg)	18
Number of Displays	1
Shipping Dimensions (hwd / in.)	2.05 x 11.61 x 16.14
Shipping Dimensions (hwd / cm)	5.21 x 29.49 x 41.00
Shipping Weight (lbs.)	2.20
Shipping Weight (kg)	1.00
Unit Dimensions (hwd / in.)	5.500 x 15.625 x 11.250
Unit Dimensions (hwd / cm)	13.97 x 39.69 x 28.76
Unit Weight (lbs.)	1.80
Unit Weight (kg)	0.82
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	No
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.