

Cat5e 350 MHz Snagless (UTP) Ethernet Cable (RJ45 M/M) - Plenum Rated, Blue, 75 ft. (22.86 m)

MODEL NUMBER: N003-075-BL-P



Highlights

- Plenum rated (CMP) Blue jacket Cat5e
- 4-Pair Solid UTP
- Slim boot allows for Easy side-by-side plugging

Package Includes

- 75-ft. (22.86 m) Cat5e Plenum Rated Snagless Patch Cable, (RJ45 M/M) - Blue

Description

This Blue plenum-rated Cat5e Ethernet cable features integral snagless strain relief. The cable is manufactured from CMP 4-pair Solid Conductor UTP for improved long-run performance, and is rated for 350 MHz/1 Gbps communication. CMP plenum-rated cable satisfies local fire and building codes for cabling run through ceilings and walls.

Features

- 75-ft. (22.86 m), Blue, Plenum rated (CMP) Cat5e Patch Cable
- Solid conductor 4-Pair for maximum signal integrity
- Rated for 350Mhz / 1Gbps communication
- Integral snagless feature protects locking tab from breaking

Specifications

OVERVIEW	
UPC Code	037332140272
Technology	Cat5/5e
CONNECTIONS	
Side A - Connector 1	RJ45 (MALE)
Side B - Connector 1	RJ45 (MALE)
Crossover Wiring	No
Connector Type	Snagless
Angled Connector	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Cable Jacket Color	Blue
Cable Jacket Rating	CMP
Cable Shielding	UTP
Conductor Material	Solid Copper
Cable Length (ft.)	75
Cable Length (m)	22.87
Cable Length (in.)	900
Cable Length (cm)	2286
Shipping Dimensions (hwd / in.)	11.75 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	29.84 x 17.78 x 1.27
Shipping Weight (lbs.)	0.19
Shipping Weight (kg)	0.09
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
FEATURES & SPECIFICATIONS	
Antibacterial	No
IP68 Rated	No
Snagless Connector	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.