




## 24-Port 1U Rack-Mount STP Shielded Cat5e/6 Feedthrough Patch Panel with 90-Degree Down-Angle Ports, RJ45 Ethernet, TAA

### MODEL NUMBER: N254-024-SH-D





Manages and organizes Cat5e/6 input and output cable connections in your high-density Ethernet network. RJ45 ports face downward to ease cable installation. Ideal for MDFs and IDFs where quick patching changes are necessary.

#### Description

The N254-024-SH-D 24-Port 1U Rack-Mount STP Shielded Cat5e/6 Feedthrough Patch Panel features RJ45 ports that point downward at a 90-degree angle to ease cable installation in hard-to-reach places. It meets or exceeds Cat6 specifications and works with USOC, T568A and T568B wiring to comply with industry standards. It's ideal for MDFs (main distribution frames) and IDFs (intermediate distribution frames) where quick patching changes are necessary.

Made from heavy-duty 14ga cold-rolled steel, the N254-024-SH-D manages and organizes the cabling in your high-density network with no 110 punchdown termination required. Just plug your Cat5e/6 cables into the 24 fully shielded RJ45 coupler jacks on both sides of the panel. Ports are clearly numbered to help you identify connections.

Mounts easily into 1U of an EIA-standard 19-inch rack. Grounding wire included. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. STP Cat6 Patch Cord

#### Features

#### Manages and Organizes High-Density Network Cabling

- Meets or exceeds Cat6 specifications
- Heavy-duty 14ga cold-rolled steel construction
- Works with USOC, T568A and T568B wiring to comply with industry standards
- · Ideal for MDFs and IDFs where quick patching changes are needed

#### 24 Fully Shielded RJ45 Coupler Jacks

- 90-degree down-angle installation for easy cable connection in hard-to-reach places
- Ports are clearly numbered for easy identification
- Low-profile form factor requires no 110 punchdown termination

#### Quick, Easy Installation

• Mounts easily into 1U of EIA-standard 19 in. rack

#### Highlights

- No 110 punchdown termination required
- Works with USOC, T568A and T568B wiring
- Heavy-duty 14ga cold-rolled steel construction
- Numbered ports for easy connection identification
- Mounts into 1U of EIA-standard 19 in. rack

#### **Package Includes**

- N254-024-SH-D 24-Port 1U Rack-Mount STP Shielded Cat5e/6 Feedthrough Patch Panel
- (24) Cat6 Shielded Snap-In Couplers (RJ45 F/F)
- Grounding wire
- Mounting hardware
- Owner's manual





• Includes grounding wire

#### **TAA-Compliant**

• Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

# **Specifications**

OVERVIEW	
UPC Code	037332197481
Product Type	Feed-Through
Technology	Cat5/5e; Cat6
CONNECTIONS	
Number of Ports	24
Side A - Connector 1	RJ45 (FEMALE)
Side B - Connector 1	RJ45 (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.80 x 2.70 x 19.60
Shipping Dimensions (hwd / cm)	7.11 x 6.86 x 49.78
Shipping Weight (lbs.)	2.20
Shipping Weight (kg)	1.00
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Warranty Details	LIFETIME LIMITED WARRANTY

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.