



PDU Power Cord, C13 to C14 - 10A, 250V, 18 AWG, 15 ft. (4.57 m), Black

MODEL NUMBER: P004-015









Computer power extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 15 ft.

Features

C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other EquipmentThis IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. This C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 15-ft. (4.57 m). The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other essential peripherals
- Adds 15-ft. (4.57 m) to your existing power connection to provide flexibility in placing devices
- C13-to-C14 PDU-style extension cord is ideal replacement for worn-out or missing cable

Applications

- Connect devices like computers, servers and monitors to a PDU up to 15-ft. (4.57 m) away in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source far from your workstation
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

 P004-015 C14 Male to C13 Female Power Cable, 15-ft. (4.57 m), Black

Specifications

•		
OVERVIEW		
UPC Code	037332180483	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU	
Country/Region	Global	
INPUT		
Maximum Input Amps	10	
Voltage Compatibility (VAC)	100-250	
CONNECTIONS		
Side A - Connector 1	IEC-320-C14	
Side B - Connector 1	IEC-320-C13	
PHYSICAL		





Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	7.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm²)	0.82
Cable Length (ft.)	15
Cable Length (m)	4.57
Shipping Dimensions (hwd / in.)	0.50 x 5.10 x 8.00
Shipping Dimensions (hwd / cm)	1.27 x 12.95 x 20.32
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); cUL Listed; UL Listed
Product Compliance	RoHS; REACH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.