

Heavy-Duty Power Extension Cord, 15A, 14AWG (Right Angle IEC-320-C14 to IEC-320-C13), 2-ft.

MODEL NUMBER: P005-002-14RA



Highlights

- 2 ft. C13 to Right-Angle C14 Power Cord
- 14 AWG x 3C, 15A, 100-250V, SJT
- UL Listed

Package Includes

- P005-002-14RA C13 to Right-Angle C14 Power Cord

Save space in tight places with this right-angle connector cord

Description

Use Tripp Lite's P005-002-14RA in server applications that require a higher rated, heavier gauge cable, and in which space is in high demand. The right-angle C14 connector on this power cord is perfect for saving space in tight areas, such as in the back of your rack enclosure cabinet. When plugged in, it seats flush against the back of a device (e.g. PDU, UPS, etc.), providing space for your rack door to close, or additional room to organize a tight area. C13 to Right-Angle C14 connectors, 3 x 14 AWG conductors, 15A rating, 100-250V, SJT jacket. Tripp Lite Lifetime Limited Warranty.

Features

- Molded, Heavy-Duty Power Cable, 2 ft.
- IEC-60320-C13 to Right-Angle IEC-60320-C14 connectors
- Right-angle C14 connector is perfect for saving space in tight areas
- 14 AWG x 3C, 15A, 100-250V, SJT jacket
- RoHS Compliant
- UL Listed

Specifications

OVERVIEW	
UPC Code	037332179913
CONNECTIONS	
Side A - Connector 1	IEC-320-C14 - RIGHT ANGLE
Side B - Connector 1	IEC-320-C13



Powering Business Worldwide



PHYSICAL	
Color	Black
Power Cord Jacket Type	SJT
Wire Gauge (AWG)	14
Cable Length (ft.)	2
Cable Length (m)	0.61
Shipping Dimensions (hwd / in.)	10.00 x 7.00 x 0.10
Shipping Dimensions (hwd / cm)	25.40 x 17.78 x 0.25
Shipping Weight (lbs.)	0.31
Shipping Weight (kg)	0.14
ENVIRONMENTAL	
Operating Temperature Range	-4 F (-20 C) to 140 F (60 C)
Storage Temperature Range	-4 F (-20 C) to 140 F (60 C)
Operating Humidity Range	10-85% RH
Storage Humidity Range	10-85% RH
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.