



# Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 6 ft. (1.83 m), Black

### MODEL NUMBER: P018-006







- 6-ft. heavy-duty power cord, C14-to-C15
- 100-250V, 15A, 14AWG, SJT
- UL Listed

#### Package Includes

• 6-ft. C14 to C15 Power Cord

Connect network hardware with C15 power connections such as servers to PDUs and UPS systems with C14 type inputs.

#### Features

- Heavy-duty power cord supports up to 250V
- Flexible 14AWG wire for easy routing
- Use with Cisco, HP and other hardware that uses C15 type power connections
- UL Listed

## **Specifications**

OVERVIEW	
	007000400440
UPC Code	037332168443
Device Compatibility	Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	15
Voltage Compatibility (VAC)	100-250
CONNECTIONS	
Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C15
PHYSICAL	





Product Warranty Period (Worldwide)	Lifetime limited warranty
WARRANTY & SUPPORT	
Product Compliance	RoHS
Product Certifications	cUL Listed; UL Listed
STANDARDS & COMPLIANCE	
Coiled Power Cord	No
Locking Plug	No
High Voltage	Yes
Angled Plug	No
Antibacterial	No
FEATURES & SPECIFICATIONS	
Storage Humidity Range	10% to 65% RH
Operating Humidity Range	10% to 65% RH
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
ENVIRONMENTAL	
	V.0*
Shipping Weight (kg)	0.76
Shipping Weight (lbs.)	0.76
Shipping Dimensions (hwd / m.)	2.54 x 17.78 x 27.94
Shipping Dimensions (hwd / in.)	1.00 x 7.00 x 11.00
Cable Length (m)	1.83
Wire Gauge (OD - mm <sup>2</sup> ) Cable Length (ft.)	2.08
Wire Gauge (AWG)	14
Number of Conductors	3
Cable Outer Diameter (OD)	9.3mm
Power Cord Jacket Type	SJT
Cable Jacket Rating	VW-1
Cable Jacket Material	
Cable Jacket Color	Black PVC
Plug Color	Black





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.