

# Power Cord C14 to C15 - Heavy-Duty, 15A, 250V, 14 AWG, 10 ft. (3.05 m), Black

MODEL NUMBER: P018-010



### Highlights

- 10-ft. heavy-duty power cord, C14-to-C15
- 100-250V, 15A, 14AWG, SJT
- UL Listed

### Package Includes

- 10-ft. C14 to C15 Power Cord

Connect network hardware with C15 power connections such as servers to PDUs and UPS systems with C14 type inputs.

### Features

- Heavy-duty power cord supports up to 250V
- Flexible 14AWG wire for easy routing
- Use with Cisco, HP and other hardware that uses C15 type power connections
- UL Listed

## Specifications

| OVERVIEW                    |                          |
|-----------------------------|--------------------------|
| UPC Code                    | 037332182562             |
| Device Compatibility        | Network Switch; UPS; PDU |
| Country/Region              | North America            |
| INPUT                       |                          |
| Maximum Input Amps          | 15                       |
| Voltage Compatibility (VAC) | 100-250                  |
| CONNECTIONS                 |                          |
| Side A - Connector 1        | IEC-320-C14              |
| Side B - Connector 1        | IEC-320-C15              |
| PHYSICAL                    |                          |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                             |
|--------------------------------------|-----------------------------|
| Plug Color                           | Black                       |
| Cable Jacket Color                   | Black                       |
| Cable Jacket Material                | PVC                         |
| Cable Jacket Rating                  | VW-1                        |
| Power Cord Jacket Type               | SJT                         |
| Cable Outer Diameter (OD)            | 9.3mm                       |
| Number of Conductors                 | 3                           |
| Wire Gauge (AWG)                     | 14                          |
| Wire Gauge (OD - mm <sup>2</sup> )   | 2.08                        |
| Cable Length (ft.)                   | 10                          |
| Cable Length (m)                     | 3.05                        |
| Shipping Dimensions (hwd / in.)      | 14.17 x 11.80 x 0.50        |
| Shipping Dimensions (hwd / cm)       | 35.99 x 29.97 x 1.27        |
| Shipping Weight (lbs.)               | 1.04                        |
| Shipping Weight (kg)                 | 0.47                        |
| <b>ENVIRONMENTAL</b>                 |                             |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range             | 10% to 65% RH               |
| Storage Humidity Range               | 10% to 65% RH               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                             |
| Antibacterial                        | No                          |
| Angled Plug                          | No                          |
| High Voltage                         | Yes                         |
| Locking Plug                         | No                          |
| Coiled Power Cord                    | No                          |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                             |
| Product Certifications               | cUL Listed; UL Listed       |
| Product Compliance                   | RoHS                        |
| <b>WARRANTY &amp; SUPPORT</b>        |                             |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty   |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.