

Power Extension Cord, NEMA 5-15P to NEMA 5-15R - 13A, 120V, 16 AWG, 15 ft. (4.57 m), Black

MODEL NUMBER: P024-015-13A



15 ft. extension cord with 5-15P and 5-15R connectors connects bulky power transformers without blocking adjacent outlets on your PDU.

Features

15-ft. (4.57 m) Extension Cord Connects PCs, Printers, Monitors and Other Equipment This cord is recommended for home/office desktop computer applications, home theater setups or other applications where multiple devices are plugged into a surge protector, PDU or UPS system. It allows you to connect bulky power adapters to a NEMA 5-15R outlet without blocking adjacent outlets. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Highlights

- Recommended for powering computers, printers and other home/office peripherals
- 15-ft. (4.57 m) length allows great flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing 15-ft. (4.57 m) extension cord

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

- P024-015-13A 15-ft. (4.57 m) Extension Cord, NEMA 5-15P to NEMA 5-15R, Black

Specifications

OVERVIEW	
UPC Code	037332197153
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	13
Voltage Compatibility (VAC)	125
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	NEMA 5-15R
PHYSICAL	



Powering Business Worldwide

TRIPP LITE
SERIES

Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	8.5mm
Number of Conductors	3
Wire Gauge (AWG)	16
Wire Gauge (OD - mm ²)	1.31
Cable Length (ft.)	15
Cable Length (m)	4.57
Cable Length (cm)	457.20
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 10.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 25.40
Shipping Weight (lbs.)	1.17
Shipping Weight (kg)	0.53
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.