



European Computer Power Cord, C13 to Schuko, 10A, 250V, 17 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P054-006











IEC 320 C13 to Schuko EU power cord transforms a C14 plug into a Schuko plug for connecting to a wall outlet, PDU or UPS system.

Features

C13 to Schuko EU Power Cord Connects Computers, Servers and Other Network Devices This Schuko to C13 European computer power cord is designed for small data center or office workstation applications that do not require a heavy-gauge connection. The cable can be used to connect a computer, server or drive to a Schuko wall outlet, UPS system or PDU or replace or upgrade a worn-out or lost power cable. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Highlights

- C13 to Schuko cable for powering computers, servers and other network devices
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for worn-out or missing EU power cable

Applications

- Connect devices like computers, monitors and printers to a PDU up to 1.8 m away in your home or office workstation
- Transform a C14 plug into a Schuko plug with no electrician needed
- Extend an existing power connection up to 1.8 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

 P054-006 C13 to Schuko, European Computer Power Cord, 6 ft. (1.8 m), Black

Specifications

OVERVIEW		
UPC Code	037332145574	
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU	
Country/Region	Europe	
INPUT		
Maximum Input Amps	10	
Voltage Compatibility (VAC)	250	
CONNECTIONS		
Side A - Connector 1	CEE 7/7 SCHUKO PLUG	
Side B - Connector 1	IEC-320-C13	
PHYSICAL		





Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.8mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm²)	0.82
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	12.80 x 8.90 x 0.50
Shipping Dimensions (hwd / cm)	32.51 x 22.61 x 1.27
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	10% to 65% RH
Storage Humidity Range	10% to 65% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	UL Listed; cUL Listed
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.