

DisplayPort to HDMI 4K Active Adapter Video Converter, DP Ver 1.2, HDCP, 4K 30Hz (M/F), 6-in. (15.24 cm)

MODEL NUMBER: P136-06N-UHD-V2



Converts a DisplayPort 1.2 audio and 4K x 2K video signal for display on an HDMI monitor, projector or television.

Features

Send High-Quality DisplayPort 1.2 Audio/Video Signals to an HDMI Display

- Connects DisplayPort 1.2 computer to HDMI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Female HDMI and male DisplayPort connectors
- Backward compatible with previous DisplayPort generations

Vibrant, Superior Video Quality

- Supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 7.1 Audio Surround Sound
- HDCP 1.3 and DPCP 1.0 compliant
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity

Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life
- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

Specifications

OVERVIEW

Highlights

- Active converter works with all DisplayPorts
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 7.1 Audio Surround Sound
- HDCP 1.3 and DPCP 1.0 compliant
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Gold-plated connectors and contacts

Package Includes

- P136-06N-UHD-V2 DisplayPort 1.2 to HDMI Active Converter (M/F), 6 in.



Powering Business Worldwide



UPC Code	037332192028
Product Type	Video Adapter
Technology	HDMI; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	Black
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
FEATURES & SPECIFICATIONS	
HDCP Specification	1.3
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.