

Keyspan Mini DisplayPort to VGA/HDMI All-in-One Video Converter Adapter, 4K 30Hz HDMI, DP1.2, White, 6-in. (15.24 cm)

MODEL NUMBER: P137-06N-HV-V2W



All-in-one converter/adapter connects your Mini DisplayPort or Thunderbolt-enabled laptop or tablet to a VGA or HDMI display without the need to carry separate adapters. Ideal for trade shows, classrooms and lecture halls.

Features

Connects Your Mini DisplayPort Laptop or Tablet to a VGA or HDMI Display

- Ideal for trade shows, classrooms, lecture halls and other presentations
- HD15 port supports video resolutions up to 1920 x 1200, including 1080p
- HDMI port supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 24/30 Hz
- Supports 36-bit Deep Color (12 bits per channel)

Plug-and-Play Convenience

- No software or drivers to install
- No external power supply required
- Small enough to stow in laptop bag or briefcase
- The P137-06N-HV-V2W is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Specifications

OVERVIEW	
UPC Code	037332193223
Product Type	Video Adapter
Technology	HDMI; DisplayPort; VGA/SVGA
CONNECTIONS	

Highlights

- Separate HD15 and HDMI female connectors
- HDMI port supports UHD 4K x 2K @ 24/30 Hz video resolutions
- The P137-06N-HV-V2W is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port
- Plug and play—no software, drivers or power supply needed
- Small size for easy carrying in laptop bag or briefcase

System Requirements

- The P137-06N-HV-V2W is a Passive adapter, and requires the connected computer to have a DP++ (Displayport ++) port

Package Includes

- P137-06N-HV-V2W Keyspan Mini DisplayPort 1.2 to VGA/HDMI All-in-One Converter Adapter, 6 in.
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (FEMALE)
Side B - Connector 2	HDMI (FEMALE)
PHYSICAL	
Color	White
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	3.90 x 4.70 x 0.50
Shipping Dimensions (hwd / cm)	9.91 x 11.94 x 1.27
Shipping Weight (lbs.)	0.15
Shipping Weight (kg)	0.07
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.