

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 1 ft. (0.31 m)

MODEL NUMBER: P560-001



Description

This DVI Dual-Link TMDS cable delivers the high performance and high bandwidth needed for today's digital video displays. Gold-plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards. A DVI Dual-Link video card is required to obtain resolutions up to 2560 x 1600. Both DVI connectors are molded and have integral strain relief for long life reliability.

Features

- DVI-D Dual Link Male-Male, 1-ft. (0.31 m)
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Gold plated copper contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- Supports 2560 x 1600 resolution
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
UPC Code	037332181244
Product Type	Passive Cable
Technology	DVI
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)

Highlights

- DVI-D Dual Link TMDS Male-Male, 1-ft. (0.31 m)
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- Monitor with DVI, and CPU with a DVI video card. Video card must support Dual Link in order to obtain resolutions up to 2560 x 1600

Package Includes

DVI Dual Link TMDS cable - DVI-D, M/M, 1-ft. (0.31 m)



Powering Business Worldwide

TRIPP LITE
SERIES

Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	1
Cable Length (m)	0.30
Cable Length (in.)	12
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	10.000 x 8.000 x 0.500
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.