

## DisplayPort 1.2 to HDMI Adapter Cable (DP with Latches to HDMI M/M), 4K, 3 ft. (0.9 m)

MODEL NUMBER: P582-003-V2



Converts a DisplayPort v1.2 audio/video signal for display on an HDMI monitor, projector or television.

### Features

#### Send High-Quality DisplayPort v1.2 Audio/Video Signals to an HDMI Display

- Connects DisplayPort computer to HDMI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- HDMI and Latching DisplayPort male connectors
- No separate adapter required

#### Vibrant, Superior Video Quality

- Supports Ultra High Definition (UHD) video resolutions up to 3840 x 2160 (4K x 2K)
- Supports audio and HDCP
- Perfect for use with Dual-Mode (DP++) DisplayPort graphics cards

#### Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Latching Displayport plug for secure connection

## Specifications

OVERVIEW	
UPC Code	037332191984
Product Type	Passive Cable
Technology	HDMI; DisplayPort
Cable Type	Passive

### Highlights

- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K)
- Supports audio and HDCP
- No separate adapter required
- Gold-plated connectors and contacts
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ dual-mode port)

### Package Includes

- P582-003-V2 DisplayPort 1.2 to HDMI Adapter Cable, 3 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	7.3mm
Wire Gauge (AWG)	28
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.18
Shipping Weight (kg)	0.08
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.