



Mini DisplayPort 1.2 to DVI Active Adapter Cable (M/M), 1080p, 3 ft. (0.9 m)

MODEL NUMBER: P586-003-DVI-V2





Highlights

- Active adapter cable for use with any Mini Displayport (or Thunderbolt) port
- Supports HD video resolution up to 1920 x 1080 (1080p)
- · No separate adapter required
- Gold-plated connectors and contacts

Package Includes

 P586-003-DVI-V2 Mini DisplayPort 1.2 to DVI Active Adapter Cable, 3 ft.

Converts a Mini DisplayPort v1.2 video signal for display on a DVI monitor, projector or television.

Features

Send High-Quality Mini DisplayPort v1.2 Video Signals to a DVI Display

- Connects Mini DisplayPort (or Thunderbolt) computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Mini DisplayPort and DVI-D male connectors
- · No separate adapter required

Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts Single-Mode and Dual-Mode (DP++) Mini DisplayPort output
- Perfect for use with graphics cards, such as AMD Eyefinity, that don't output DP++ signals

Superior Materials for Superior Performance

- Double shielding with foil and braid for maximum EMI/RFI protection
- · Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life

Specifications

OVERVIEW		
UPC Code	037332192004	
Product Type	Active Cable	
Technology	DVI; DisplayPort	
Cable Type	Active	





VIDEO		
Max Supported Video Resolution	1920 x 1200 (1080p)	
Max Supported Color Depth	12-bit True Color	
HDR Support	No	
Chroma Sub Sampling	4:4:4; 4:2:2	
CONNECTIONS		
Side A - Connector 1	MINI DISPLAYPORT (MALE)	
Side B - Connector 1	DVI-D DUAL-LINK (MALE) (WIRED TO DVI-D SINGLE-LINK)	
Connector Plating	Gold	
Contact Plating	Gold	
Latching or Gripping Connector	No	
PHYSICAL		
Color	Black	
Material of Construction	ABS, PVC	
Cable Jacket Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	4.8 mm	
Wire Gauge (AWG)	32	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Cable Length (in.)	36	
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50	
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27	
Shipping Weight (lbs.)	0.21	
Shipping Weight (kg)	0.10	
ENVIRONMENTAL		
Operating Temperature Range	32° to 113°F (0° to 45°C)	
Storage Temperature Range	14° to 176°F (-10° to 80°C)	
Operating Humidity Range	10% to 85%, Non-Condensing	
Storage Humidity Range	5% to 90%, Non-Condensing	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	





IP20 Rated	No	
Displayport Specification	1.2	
HDCP Specification	1.4	
STANDARDS & COMPLIANCE		
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	3-year limited warranty	
Product Warranty Period (U.S. & Canada)	3-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.