

Mini DisplayPort to VGA Active Adapter Cable (M/M), 6 ft. (1.8 m)

MODEL NUMBER: P586-006-VGA



Connects a VGA monitor to a computer with Mini Displayport with a single cable

Description

The P586-006-VGA allows you to connect a desktop or laptop computer with Mini DisplayPort video output to a VGA-enabled monitor. All in one six-foot (1.8-meter) plug-and-play design with in-line signal converter requires no additional adapters or software. It features a low-profile VGA connector that fits neatly into the available monitor space without jamming between the wall and the back of the display or impeding neighboring connectors. Resolution support up to 1920 x 1200. Unlike passive adapters, active adapters convert both Single-Mode and Dual-Mode (DP++) DisplayPort output. It is ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual-Mode (DP++) signals.

Features

- 6-ft. (1.83 m) Mini Displayport Male to VGA Male cable
- 1920x1200 resolution
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) DisplayPort output

Specifications

OVERVIEW	
UPC Code	037332180759
Product Type	Active Cable
Technology	VGA/SVGA; DisplayPort
Cable Type	Active
VIDEO	

Highlights

- Connect a Mini Displayport computer port to a VGA monitor
- Low-profile VGA connector fits neatly into available space; no jamming between wall and monitor or impeding neighboring connections
- Ideal for use with graphics cards, such as AMD Eyefinity, that do not output Dual Mode (DP++) signals
- Converts both Single-Mode and Dual Mode (DP++) Displayport output
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- VGA Monitor
- Computer with Mini Displayport
- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P586-006-VGA-V2

Package Includes

- 6-ft. (1.83 m) Mini Displayport to Active VGA Cable, M/M



Powering Business Worldwide

TRIPP LITE
SERIES

Max Supported Video Resolution	1920 x 1200 (1080p)
HDR Support	No
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HD15 (MALE)
Connector Plating	Nickel
Contact Plating	Gold
Latching or Gripping Connector	No
PHYSICAL	
Color	Black
Material of Construction	ABS, PVC
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.0 +/- 15mm
Wire Gauge (AWG)	32
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.24
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	7.000 x 9.000 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Operating Humidity Range	0% to 85%, Non-Condensing
Storage Humidity Range	0% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
Displayport Specification	1.1a



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; Trade Agreements Act (TAA); UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty
Product Warranty Period (U.S. & Canada)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.