

400W PowerVerter Ultra-Compact Car Inverter with 2 AC/2USB - 3.1A/Battery Cables/Cigarette Lighter Adapter (CLA)

MODEL NUMBER: PV400USB



Charge and/or power multiple electronic devices—including smartphones, laptops, tablets, GPS units, DVD players, MP3 players, camping equipment and mobile office equipment—on the go in your car, truck, boat or RV.

Description

The PV400USB 400W PowerVerter® Ultra-Compact Car Inverter provides 400 watts of portable power for charging and operating multiple devices in your car, truck, boat or RV. It converts 12V DC power into standard 120V AC power to run a wide variety of electronics, such as laptops, smartphones, tablets, game systems, portable TVs and DVD players, MP3 players and GPS units, as well as low-power lights, camping accessories, battery rechargers for small battery-operated power tools and mobile office equipment.

The PV400USB features two AC outlets, a 2.1A USB port and a 1.0A USB port. Just plug the DC input jack with convenient 3-ft. (0.91 m) cord into the 12V cigarette lighter socket in your vehicle, or use the battery cables to connect to your battery - always connect red to red and black to black. Press the on/off button, and the unit is ready to operate. Easy-to-read LED lets you know the inverter is receiving power from the battery.

To prevent you from running down your car battery, the PV400USB turns off automatically when the input voltage falls to 10V. Likewise, the unit will also shut down if it gets too hot (for instance, because your connected devices exceed 400 watts). A built-in ventilation fan keeps the interior cool during extended use. The durable plastic housing is engineered to withstand the rigors of road trips, campouts, business trips and family vacations. No maintenance is required.

Features

Powers and Charges Up to 4 Devices

- Converts 12V DC battery power to standard 120V AC power
- Runs smartphones, laptops, tablets, GPS units, game systems, portable TVs, DVD players, MP3 players and other electronics
- Features 2 AC outlets, 2.1A USB port and 1.0A USB port
- Outputs 400 watts (continuous); 800 watts (peak)

Easy to Use

- DC jack plugs into the cigarette lighter socket in your car, truck, boat or RV
- Battery Cables connect directly to the battery - Always connect red to red and black to black.

Highlights

- Charges multiple electronic devices in your vehicle
- Features 2 AC outlets, 2.1A USB port and 1.0A USB port
- Battery Cables for direct connect
- CLA plugs your vehicle's cigarette lighter socket
- Built-in interior cooling fan
- Durable plastic housing

Package Includes

- PV400USB 400W PowerVerter Ultra-Compact Car Inverter
- Red/Black Battery Cables
- CLA adapter
- Warranty information
- Owner's Manual



Powering Business Worldwide



- Flexible 3-ft. (0.91 m) cords allows devices to run in the back seat
- LED indicates the unit is receiving power from the battery

Premium Construction

- Durable plastic housing built to withstand rigors of travel
- Built-in ventilation fan keeps the interior cool during extended use
- Automatic low-voltage shutoff prevents deep vehicle battery discharge at 10V
- No maintenance required

Specifications

| OVERVIEW | |
|-------------------------------------|---|
| UPC Code | 037332187895 |
| INPUT | |
| Input Connection Type | 12VDC cigarette lighter input plug connection or battery cables |
| Voltage Compatibility (VDC) | 12 |
| Input Cord Length (ft.) | 3 |
| Input Cord Length (m) | 0.91 |
| OUTPUT | |
| Frequency Compatibility | 60 Hz |
| Pure Sine Wave Output | No |
| Nominal Output Voltage(s) Supported | 120V |
| Output Receptacles | (2) 5-15R |
| Continuous Output Capacity (Watts) | 400 |
| Peak Output Capacity (Watts) | 800 |
| Output Frequency Regulation | 60 Hz (+/- 3 Hz) |
| Overload Protection | 40A fuse |
| BATTERY | |
| DC System Voltage (VDC) | 12 |
| CHARGING | |
| Charging Ports / Amps | (1) 1A; (1) 2.1A |
| PHYSICAL | |
| Material of Construction | Plastic |
| Shipping Dimensions (hwd / in.) | 6.89 x 5.71 x 2.56 |

| | |
|-------------------------------------|-------------------------|
| Shipping Dimensions (hwd / cm) | 17.50 x 14.50 x 6.50 |
| Shipping Weight (lbs.) | 1.70 |
| Shipping Weight (kg) | 0.77 |
| Unit Dimensions (hwd / in.) | 2.362 x 4.173 x 5.961 |
| Unit Dimensions (hwd / cm) | 15/14 x 10.59 x 5.99 |
| Unit Weight (lbs.) | 1.217 |
| Unit Weight (kg) | 0.55 |
| STANDARDS & COMPLIANCE | |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.