



# Protect It! 3-Outlet Surge Protector, Direct Plug-In, 660 Joules, 2 Diagnostic LEDs

MODEL NUMBER: SK3-0











### **Highlights**

- 3 outlets/direct plug-in
- 660 joule rating
- Diagnostic LEDs

#### **Package Includes**

• SK3-0 surge suppressor

### **Description**

The SK3-0 surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 3 outlets and 660 joules of surge energy absorption. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

#### **Features**

- 3 outlets / direct plug-in
- Surge suppression rating: 660 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
  equipment damage and indicating replacement is required

## **Specifications**

| OVERVIEW                           |                |  |
|------------------------------------|----------------|--|
| UPC Code                           | 037332166319   |  |
|                                    |                |  |
| INPUT                              |                |  |
| Nominal Input Voltage(s) Supported | 120V AC        |  |
| Recommended Electrical Service     | 120V           |  |
| Input Cord Length Details          | Direct Plug-In |  |
| Voltage Compatibility (VAC)        | 120            |  |
| Maximum Surge Amps                 | 39000          |  |





| Input Plug Type                     | NEMA 5-15P   |  |
|-------------------------------------|--|--|
| Input Cord Length (ft.)             | 0  |  |
| Right-Angle Plug                    | No   |  |
| Input Cord Length (m)               | 0.00   |  |
| Integrated Cord Clip                | No   |  |
| OUTPUT                              |  |  |
| Frequency Compatibility             | 60 Hz  |  |
| Output Receptacles                  | (3) 5-15R  |  |
| Circuit Breaker (amps)              | 15   |  |
| Transformer Accommodation           | (2) Yes  |  |
| Right-Angle Outlets                 | No   |  |
| USER INTERFACE, ALERTS & CONTROLS   |  |  |
| Diagnostic LED(s)                   | Yes  |  |
| SURGE / NOISE SUPPRESSION           |  |  |
| AC Suppression Joule Rating         | 660  |  |
| AC Suppression Response Time        | < 1ns  |  |
| Protection Modes                    | Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression |  |
| AC Suppression Surge Current Rating | 27,000   |  |
| UL1449 Let Through Rating           | 500, 400, 500  |  |
| EMI / RFI Filtering                 | Yes  |  |
| Immunity                            | Conforms to IEE 587/ANSI C62.41  |  |
| Automatic Shut-Off                  | Yes  |  |
| DATALINE SURGE SUPPRESSION          |  |  |
| Cable (Coax) Protection             | No   |  |
| Network (Ethernet) Protection       | No   |  |
| Telephone/DSL Protection            | No   |  |
| PHYSICAL                            |  |  |
| Material of Construction            | Plastic  |  |
| Mounting Holes or Slots             | No   |  |
| Receptacle Color                    | Gray   |  |
| Shipping Dimensions (hwd / in.)     | 5.90 x 3.00 x 2.70   |  |
| Shipping Dimensions (hwd / cm)      | 14.99 x 7.62 x 6.86  |  |
|                                     |  |  |





| ·  |
|--|
| 0.32   |
| 0.15   |
| 2.500 x 3.800 x 2.100  |
| 6.35 x 9.7 x 5.33  |
| .20  |
| 0.09   |
|  |
|  |
| No   |
| No   |
|  |
|  |
| UL 1449  |
| RoHS   |
|  |
|  |
| Lifetime limited warranty  |
| \$5,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |
|  |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks

are the property of their respective owners.