



Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 3.4 A USB Charger, Diagnostic LED

MODEL NUMBER: SK30USB











Highlights

- 3 outlets/direct plug-in
- 540 joule rating
- 3.4 amp USB charging
- Diagnostic LED

Package Includes

• SK30USB surge suppressor

Description

The SK30USB surge suppressor offers reliable surge and line noise protection. The compact direct plugin design allows for easy portability and features 3 outlets and 540 joules of surge energy absorption. Diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 3.4 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 3 outlets / direct plug-in
- Surge suppression rating: 540 joules
- 3.4 amp USB Charger
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing
 equipment damage and indicating replacement is required

Specifications

OVERVIEW		
UPC Code	037332180353	
Product Type	Surge Protector	
Charging Form Factor	Direct Plug-In	
Device Compatibility	Phone; Tablet; Amazon Kindle	
INPUT		





Nominal Input Voltage(s) Supported	120V AC		
Recommended Electrical Service	120V		
Input Cord Length Details	Direct Plug-In		
Voltage Compatibility (VAC)	120		
Input Plug Type	NEMA 5-15P		
Input Cord Length (ft.)	0		
Right-Angle Plug	No		
Input Cord Length (m)	0.00		
Integrated Cord Clip	No		
OUTPUT			
Frequency Compatibility	60 Hz		
Output Receptacles	(3) 5-15R		
Circuit Breaker (amps)	15		
Transformer Accommodation	(2) Yes		
Right-Angle Outlets	No		
USER INTERFACE, ALERTS & CONTROLS			
Diagnostic LED(s)	Yes		
Diagnostic LED Details	Green - Protected		
CHARGING			
Number of Charging Ports	2		
Total Charging Watts	10.5		
Charging Method	USB		
Charging Port Type	USB A (FEMALE)		
Charging Ports / Amps	(2) 2.1A		
Overcharge Protection	No		
SURGE / NOISE SUPPRESSION			
AC Suppression Joule Rating	540		
AC Suppression Response Time	<1 ns		
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression		
AC Suppression Surge Current Rating	27,000		
UL1449 Let Through Rating	500, 400, 500		
EMI / RFI Filtering			
EIVII / KEI FIILEIIIIIg	Yes		





Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Plastic	
Housing Color	Black	
Mounting Holes or Slots	No	
Receptacle Color	Black	
Shipping Dimensions (hwd / in.)	6.30 x 2.70 x 4.00	
Shipping Dimensions (hwd / cm)	16.00 x 6.86 x 10.16	
Shipping Weight (lbs.)	0.60	
Shipping Weight (kg)	0.27	
Unit Dimensions (hwd / in.)	5.280 x 3.740 x 1.180	
Unit Dimensions (hwd / cm)	13.40 x 9.50 x 3.00	
Unit Weight (lbs.)	0.41	
Unit Weight (kg)	0.19	
Input Cord Color	Black	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
GaN Technology	No	
STANDARDS & COMPLIANCE		
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 42 (Canada); NOM (Mexico); UL 1449; UL 497A	
Product Compliance	RoHS	
1 Todact Compilance		
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance	





1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.