

1-Outlet Personal Surge Protector, Direct Plug-In, 600 Joules, 2 Diagnostic LEDs

MODEL NUMBER: **SPIKECUBE**



Highlights

- 1 outlet / direct plug-in
- 600 joule rating
- Diagnostic LEDs

Package Includes

- SPIKECUBE Surge Suppressor
- Warranty and instruction information

Description

The SPIKECUBE Surge Suppressor is a direct plug-in suppressor providing protection on one AC outlet. Its small size makes it ideal for protecting laptop computers, projectors and other portable electronics. A green "Protected" and red "Grounded" LED illuminates to indicate that adequate surge suppression is available. The unit has 600 joules of surge energy absorption.

Features

- 1 outlet; direct plug-in
- Surge energy absorption: 600 joules; 6,500 amps
- Diagnostic LEDs indicate protection present (green) and ground present (red)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
UPC Code	037332010643
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
Maximum Surge Amps	36000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0



Powering Business Worldwide



Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(1) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(1) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Protected (green) & Grounded (red)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	600
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	400, 500, 500
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Form Factors Supported	Direct plug in suppressor supports wall-mounting directly into AC receptacle
Housing Color	Light Gray
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	6.50 x 4.00 x 2.00
Shipping Dimensions (hwd / cm)	16.51 x 10.16 x 5.08
Shipping Weight (lbs.)	0.23
Shipping Weight (kg)	0.10
Unit Dimensions (hwd / in.)	2.500 x 1.900 x 1.800



Powering Business Worldwide



Unit Dimensions (hwd / cm)	6.35 x 4.83 x 4.57
Unit Weight (lbs.)	.100
Unit Weight (kg)	0.05
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1449; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 & Ultimate Lifetime Insurance

1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
 Eaton is a registered trademark. All other trademarks
 are the property of their respective owners.