

Important Note

Power strips used within the patient care vicinity may be permanently attached so that it is only removable with a tool. Choose the PSCLAMP for a safe and secure mounting solution.

Safe-IT UL 60601-1 Medical-Grade Surge Protector for Patient-Care Vicinity, 4x Hospital-Grade Outlets, 6 ft. Cord, Antimicrobial Protection

MODEL NUMBER: SPS406HGULTRA



Full 60601-1 compliance and agency listing, surge protection, integrated locking safety covers and a 6 ft. cord make this medical-grade power strip ideal for standalone use in areas inside and outside patient-care vicinities.

Features

Power Distribution Anywhere in Any Medical Facility Ideal for standalone use in all patient-care vicinities, therapy rooms, imaging environments, laboratories and administrative areas 120V, 50/60 Hz power strip complies with UL 60601-1 and UL 60950-1 specifications Automatic single-fault protection Tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 Canadian standards Patent # 7,375,939 & 8,339,759

Exclusive Antimicrobial Protection Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products

Versatile Medical-Grade Solution 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power 6 ft. power cord with NEMA 5-15P-HG plug provides ample reach to the power source Rugged all-metal housing for long life in demanding environments

Premium Safety Features 1410 joules of surge suppression protect against dangerous power spikes Integrated locking outlet safety covers block access to unused outlets Built-in 15A resettable circuit breaker protects against dangerous overloads Switchless design prevents accidental shut-off LED indicates power is present and surge-protected

Ready to Use Right Out of the Box Built-in mounting slots and flanges for easy installation on a variety of surfaces

Highlights

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for standalone use in all patient-care vicinities
- Listed to UL 60601-1 and UL 60950-1 specifications
- 1410 joules of surge suppression
- Automatic single-fault detection for added patient protection

Package Includes

- SPS406HGULTRA UL 60601-1 Medical-Grade Power Strip
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332194091
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
LED Indicators	Proper wiring and surge protection working
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1410
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	



Powering Business Worldwide



Material of Construction	Metal
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	Yes
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.40 x 5.80 x 14.40
Shipping Dimensions (hwd / cm)	6.10 x 14.73 x 36.58
Shipping Weight (lbs.)	2.60
Shipping Weight (kg)	1.18
Unit Dimensions (hwd / in.)	1.500 x 13.750 x 2.500
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Weight (lbs.)	3.20
Unit Weight (kg)	1.45
Mounting Details	Includes flanges
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
Antibacterial	No
STANDARDS & COMPLIANCE	
Patented	Patent# 7,375,939; Patent# 8,339,759
Product Certifications	CAN/CSA-C22.2 No. 601.1; CAN/CSA-C22.2 No. 601.1-M90 (Canada); CAN/CSA-C22.2 No. 60950-1 (Canada); UL 60950-1; UL 60601-1
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.