

SmartRack 2U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: SRWF2U36



Wall-mount cabinet secures and organizes 2U of 19-inch rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 36 inches deep, but extends less than 5 inches from wall.

Description

The SRWF2U36 SmartRack 2U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 lbs (68 kgs).

Because the low-profile cabinet mounts vertically, it extends less than five inches from the wall while housing equipment up to 36 inches deep, including 1U servers, UPS systems, battery packs and switches. In addition to 2U of rack space in the primary mounting area, it also includes a slide-out 1U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The front door locks securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right.

Convenient top and bottom ports allow easy cable routing.

The SRWF2U36 comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

Features

Saves Valuable Workspace Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
Houses EIA-standard 19 in. rack equipment in 2U of space
Low-profile vertical-mount cabinet extends less than 5 in. from the wall while housing equipment up to 36 in. deep, including 1U servers, UPS systems, battery packs and switches
Also includes a slide-out 1U mounting bracket at the top of the enclosure for patch panels up to 2.5 in. deep
Maximum load capacity of 150 lbs (68 kgs)

Keeps Important Equipment Secure Reversible front door locks securely to help prevent damage, tampering or theft
Vented cabinet keeps equipment cool
Convenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment Installation Ships fully assembled for quick installation
Wall-mounting holes spaced 16 in. apart for standard wall stud placement
Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in
Threaded mounting holes support M6 or 12-24 mounting
Rack spaces marked for easy reference

Meets Payment Card Industry Standards Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 2U of 19 in. rack equipment up to 36 in. deep
- Includes additional 1U of space for patch panels
- Ships fully assembled for quick installation

Package Includes

- SRWF2U36 SmartRack 2U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



Powering Business Worldwide



Specifications

OVERVIEW	
UPC Code	037332190604
Device Compatibility	Network Switch; Patch Panel; Server
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	2U
Rack Depth	Standard
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Shipping Dimensions (hwd / in.)	9.44 x 31.10 x 48.03
Shipping Dimensions (hwd / cm)	23.98 x 78.99 x 122.00
Shipping Weight (lbs.)	64.00
Shipping Weight (kg)	29.03
Unit Dimensions (hwd / in.)	43.000 x 25.600 x 4.500
Unit Dimensions (hwd / cm)	109.22 x 65.02 x 11.43
Unit Weight (lbs.)	58.86
Unit Weight (kg)	26.70
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.