

208/240V Single Phase Whip in 30 ft. (9.14 m) length with L6-30R for Breakered 3-Phase Distribution Cabinets

MODEL NUMBER: **SUWL630C-30**



Highlights

- 208/240V single phase whip distribution cabinet accessory
- 30-ft. (9.14 m) length with 3-ft. (0.91 m) removed outer jacket
- 3 conductor 10AWG stranded wire
- L6-30R outlet (208/240V 30A)

Description

208/240V single phase whip with L6-30R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 30-ft. (9.14 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks. L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection.

Features

- 208/240V single phase whip with L6-30R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 30-ft. (9.14 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB230 circuit breaker in SUDC208V series 3 phase distribution racks
- L6-30R outlet is compatible with 208/240V loads and Power Distribution Units (PDUs) supporting a L6-30P plug-in connection

Specifications

OVERVIEW	
UPC Code	037332156228
Product Type	Single-Phase Whip Cable
Accessory Type	Single-Phase Whip Cable
Accessory Class	PDU Accessories
INPUT	
Input Connection Type	Hardwire (3 wire - L, N, G)



Powering Business Worldwide



OUTPUT	
PDU Recommendation Notes	Compatible with all PDU brands fitted with a L6-30P (30A 208/240V) input plug, including Tripp Lite PDU1230 ; PDUV30HV ; PDUMH30HV ; PDUMV30HV ; PDUMNH30 ; PDUMH30HV19NET ; PDUMH30HVNET ; and PDUMV30HVNET
Output Receptacles	(1) L6-30R
PHYSICAL	
Color	Black
Cable Length (ft.)	30
Cable Length (m)	9.15
Shipping Dimensions (hwd / in.)	6.30 x 12.00 x 12.00
Shipping Dimensions (hwd / cm)	16.00 x 30.48 x 30.48
Shipping Weight (lbs.)	11.20
Shipping Weight (kg)	5.08
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.