



# Multi-Function Cable Tester with Wire Tracker and Tone Generator

MODEL NUMBER: T012-001-K











Multi-function kit for tracking cable, locating a short or breakage in a non-powered cable, and mapping RJ45 wire. Essential for cable installers or anyone in the telecom or LAN environments.

#### **Description**

The T012-001-K Multi-Function Cable Tester is an essential tool for cable installers or anyone working in telecom or LAN environments. It allows you to track cable, find a short or breakage in non-powered wires, and perform wire mapping on RJ45 cables, detecting shorts and open wires. Powered by included 9-volt batteries in the main tester and remote probe unit, the T012-001-K can find an RJ11, RJ45 or BNC cable nestled within a group of cables. The probe unit's LED flashlight is handy for working in dark areas. Included headphones help you work in noisy environments. An adjustable volume button lets you fine-tune the tone generator.

#### **Features**

# Essential Tool for Cable Installers or Telecom/LAN Personnel

- Find RJ11, RJ45 or BNC cable among group of cables
- Find short or breakage in non-powered wires
- Perform wire mapping on RJ45 cables, detecting shorts and open wires

## **Designed to Make Your Work Easier**

- LED flashlight for poking around dark areas
- · Headphones for working in noisy environments
- Volume control for fine-tuning the tone generator
- Powered by included 9V batteries
- Stores away in convenient carrying case

# **Specifications**

OVERVIEW	
UPC Code	037332189912

## **Highlights**

- Find an RJ11, RJ45 or BNC cable among group of cables
- Find a short or breakage in nonpowered wires
- Perform wire mapping on RJ45 cables
- LED flashlight on remote probe unit
- Included headphones for use in noisy areas

#### **Package Includes**

- · Main tester
- Remote probe unit
- RJ45 jumper cable
- RJ11 jumper cable
- · Alligator clip adapter
- Headphones
- (2) 9V batteries
- · Carrying case
- · Owner's manual





Accessory Type	Cable Tester	
Technology	Cat5/5e; Cat6; Cat6a	
PHYSICAL		
TITISICAL		
Shipping Dimensions (hwd / in.)	9.72 x 5.91 x 1.81	
Shipping Dimensions (hwd / cm)	24.69 x 15.01 x 4.60	
Shipping Weight (lbs.)	1.21	
Shipping Weight (kg)	0.55	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	2-year limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.