



Dual-Port USB Car Charger for Tablets and Cell Phones, 5V 4.8A (24W)

MODEL NUMBER: U280-C02-S2



Auto-sensing USB ports allow you to charge 2 mobile devices, such as a tablet and cell phone, in your vehicle at the same time.

Description

The U280-C02-S2 Dual-Port USB Car Charger lets you quickly and safely charge two USB-powered mobile devices in your vehicle at the same time. You and your passenger can connect your cell phones simultaneously to ensure full charges when you reach your destination. Also recommended for tablets, MP3 players and other USB devices, the U280-C02-S2 features two 5V 2.4A USB ports. The auto-sensing ports automatically adjust to the appropriate power level and platform, whether your device is an Apple, Android or other. This ultra-compact charger works with any standard 12V DC vehicle power outlet.

Features

Charge 2 Mobile Devices in Your Vehicle at the Same Time

- Recommended for cell phones, tablets, e-readers and MP3 players
- Each USB port supports up to 5V 2.4A
- Auto-sensing ports adjust to appropriate power level and platform (Apple, Android, etc.)
- Works with any standard 12V DC vehicle power outlet

Specifications

| OVERVIEW | | |
|----------------------|------------------------------|--|
| UPC Code | 037332196316 | |
| Product Type | Car Charger | |
| Charging Form Factor | Direct Plug-In | |
| Device Compatibility | Phone; Tablet; Amazon Kindle | |
| Technology | USB | |
| INPUT | | |

Highlights

- Recommended for cell phones, tablets, e-readers and MP3 players
- Each USB port supports up to 5V 2.4A
- Auto-sensing ports adjust to appropriate power level
- Compatible with Apple, Android and other platforms
- Works with any standard 12V DC vehicle power outlet

Package Includes

 U280-C02-S2 Dual-Port USB Car Charger for Tablets and Cell Phones, 5V 4.8A (24W)





| Nominal Input Voltage(s) Supported | 12V DC | |
|------------------------------------|-------------------------------------|--|
| Input Connection Type | Automatic Vehicle Cigarette Lighter | |
| Input Plug Type | Car Auxiliary Power Outlet | |
| OUTPUT | | |
| Output Capacity (Watts) | 24 | |
| Overload Protection | Yes | |
| CONNECTIONS | | |
| Number of Ports | 2 | |
| Side A - Connector 1 | Car Cigarette Lighter | |
| Side B - Connector 1 | (2) USB A (FEMALE) | |
| CHARGING | | |
| Number of Charging Ports | 2 | |
| Total Charging Amps | 4.8A | |
| Total Charging Watts | 24 | |
| Charging Method | USB | |
| Charging Port Type | (2) USB A (FEMALE) | |
| Charging Ports Details | USB-A: 5V/2.4A | |
| Charging Ports / Amps | (2) 2.4A | |
| Compatible Devices | Laptop; Smartphone; Tablet | |
| PHYSICAL | | |
| Color | White | |
| Shipping Dimensions (hwd / in.) | 0.50 x 3.20 x 4.40 | |
| Shipping Dimensions (hwd / cm) | 1.27 x 8.13 x 11.18 | |
| Shipping Weight (lbs.) | 0.07 | |
| Shipping Weight (kg) | 0.03 | |
| Unit Dimensions (hwd / in.) | 0.000 × 0.000 × 0.000 | |
| ENVIRONMENTAL | | |
| Operating Temperature Range | 32° to 104°F (0° to 40°C) | |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) | |
| Operating Humidity Range | 30% to 90% RH, Non-Condensing | |
| Storage Humidity Range | 10% to 90% RH, Non-Condensing | |
| FEATURES & SPECIFICATIONS | | |





| GaN Technology | No | |
|--|------------------------------|--|
| Overcurrent Protection | Yes | |
| Overvoltage Protection | Yes | |
| STANDARDS & COMPLIANCE | | |
| Product Compliance | CE (Europe); FCC (USA); RoHS | |
| WARRANTY & SUPPORT | | |
| Product Warranty Period (Worldwide) | 2-year limited warranty | |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.