

USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable (M/F), 3 ft. (0.91 m)

MODEL NUMBER: U324-003-KJ



Adds a USB 3.0 Type-A female port to a universal keystone wallplate, outlet box or panel. Ideal for giving your conference room a professional, clutter-free look.

Features

Mount a USB 3.0 Type-A Port in a Fixed Location

- USB-A female keystone jack connector snaps easily into universal keystone wallplate, outlet box or panel
- Gives your conference room a professional, clutter-free look
- Connects computers, keyboards, external hard drives, flash drives and other USB-A devices
- Data transfer rates up to 5 Gbps
- Bi-directional data interface allows data to flow both directions
- Backward compatible with earlier USB generations

Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding for error-free signal quality and EMI/RFI protection
- Molded nickel-plated connectors and gold-plated copper contacts
- Integral strain relief for long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332192424
Technology	USB 3.x
Cable Type	Passive

Highlights

- Connects two USB-A devices, such as computers and flash drives
- Data transfer rates up to 5 Gbps
- Data flows both directions simultaneously
- Twisted 28/24 data/power lines
- Backward compatible with earlier USB generations

Package Includes

- U324-003-KJ USB 3.0 SuperSpeed Keystone Jack Type-A Extension Cable (M/F), 3 ft.



Powering Business Worldwide



CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Blue
Cable Length (ft.)	3
Cable Length (m)	0.91
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.13
Shipping Weight (kg)	0.06
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.