

USB 3.0 SuperSpeed Extension Cable (A M/F), Black, 6-in. (15.24 cm)

MODEL NUMBER: U324-06N-BK



Extends your existing USB 3.0 connection by 6 in.

Features

Extend an Existing USB 3.0 Cable an Extra 6 in.

- Female USB-A connector attaches to current USB 3.0 cable

Enjoy SuperSpeed Transfer Rates in High-End Applications

- Supports data transfer rates up to 5 Gbps—10X the speed of USB 2.0
- Bi-directional interface allows data to flow both directions at the same time, increasing theoretical bandwidth by 10X

Premium Construction for Superior Signal Transfer

- Premium foil and braid shielding blocks EMI/RFI interference
- Molded nickel-plated connectors ensure excellent connectivity
- Integral strain relief for cable and connectors' long life
- Twisted 28/24 AWG data/power lines
- Rugged PVC jacket

Specifications

OVERVIEW	
UPC Code	037332193513
Technology	USB 3.x
Cable Type	Passive
CONNECTIONS	

Highlights

- Supports data transfer rates up to 5 Gbps
- Bi-directional interface allows data to flow both directions
- Backward compatible with previous USB generations
- Double-shielded protection against EMI/RFI
- Molded nickel-plated conductors

Package Includes

- U324-06N-BK USB 3.0 SuperSpeed Type-A Extension Cable (M/F), Black, 6 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	USB 3.0 A (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold
Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	5.5MM
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 3.0 (up to 5 Gbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.