



USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure with Built-In Cable and UASP Support

MODEL NUMBER: U357-025-UASP











Connects a 2.5 in. SATA hard disk drive or solid state drive to your laptop, netbook or notebook computer's USB port for extra storage and fast data transfer. UASP enabled for 70% more speed with UASP host controller.

Description

The U357-025-UASP USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure is a quick, easy way to connect a SATA HDD (Hard Disk Drive) or SSD (Solid State Drive) to your laptop, netbook or notebook's USB port. Not only does it support USB 3.0 data transfer rates up to 5 Gbps, but its UASP (USB Attached SCSI Protocol) feature reduces latency and allows it to perform up to 70% faster when connected to a UASP-enabled host controller.

Perfect for storing and sharing large files like photos, music and video files, the enclosure is compatible with 2.5-inch SATA drives up to 3 TB. Just insert the drive into the SATA connector, connect the included one-foot USB 3.0 Micro-B cable to your computer, and slide the protective cover over the drive, even when it's in use, to keep it dust-free at all times.

The U357-025-UASP accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives, as well as USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds. A blue LED flashes to indicate data transfer is occurring. After thirty minutes of inactivity, the enclosure goes into hibernation mode and wakes up when activity resumes. No software, drivers or external power supply is required. Compatible with Windows, Mac and Linux.

Features

Quickly Connects a SATA Drive to Your Computer's USB Port

- Ideal for storing large files like photos, music and video files and sharing them on your laptop, netbook or notebook
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Features UASP (USB Attached SCSI Protocol) for performance up to 70% faster when connected to UASP-enabled host controller
- · Hibernates after 30 minutes of inactivity
- Compatible with Windows, Mac and Linux

Compatible with 2.5 in. SATA Drives Up to 3 TB

- Accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives
- Backward compatible with USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds

Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Compatible with 2.5 in. SATA HDDs and SSDs up to 3 TB
- Protective cover keeps SATA drive free of dust
- Requires no software, drivers or external power supply

System Requirements

- Device with USB port (USB 3.0 required for USB 3.0 speeds)
- UASP-enabled host controller required for UASP performance
- 2.5 in. SATA HDD or SSD with 9.5 mm maximum height

Package Includes

- U357-025-UASP USB 3.0 SuperSpeed External 2.5 in. SATA Hard Drive Enclosure
- USB 3.0 Micro-B cable, 1 ft.
- Owner's manual





• Works with both HDDs (Hard Disk Drives) and SSDs (Solid State Drives)

Easy to Use Right from the Box

- Plug and play—no software, drivers or external power supply needed
- SATA drive slides easily into convenient slot
- Protective cover keeps dust and dirt away from sensitive SATA drives
- Blue LED indicates successful data transfer
- 1 ft. USB 3.0 Micro-B cable included

Specifications

| OVERVIEW | | |
|-----------------------------------|------------------------------|--|
| UPC Code | 037332190000 | |
| Drives Supported | 2.5" HDD and SSD | |
| Technology | SATA/eSATA | |
| INPUT | | |
| Bus Powered | Yes | |
| POWER | | |
| Power Consumption (Watts) | 5.00 | |
| CONNECTIONS | | |
| Number of Ports | 1 | |
| Side A - Connector 1 | USB 3.0 A (MALE) | |
| Side B - Connector 1 | 22 PIN SATA + POWER (FEMALE) | |
| Connector Plating | Nickel | |
| USER INTERFACE, ALERTS & CONTROLS | | |
| LED Indicators | Blue (Read, Write, Power) | |
| PHYSICAL | | |
| Color | Black | |
| Material of Construction | ABS | |
| Cable Jacket Color | Black | |
| Cable Length (ft.) | 0.2 | |
| Cable Length (m) | 0.06 | |
| Shipping Dimensions (hwd / in.) | 1.89 x 7.13 x 5.04 | |
| Shipping Dimensions (hwd / cm) | 4.80 x 18.11 x 12.80 | |





| Shipping Weight (lbs.) | 0.40 | |
|--|--|--|
| Shipping Weight (kg) | 0.18 | |
| Unit Dimensions (hwd / in.) | 0.591 x 4.764 x 3.071 | |
| Unit Dimensions (hwd / cm) | 1.5 x 12.1 x 7.8 | |
| Unit Packaging Type | Вох | |
| Unit Weight (lbs.) | 0.11 | |
| Unit Weight (kg) | 0.05 | |
| ENVIRONMENTAL | | |
| Operating Temperature Range | 50° to 122°F (10° to 50°C) | |
| Storage Temperature Range | 32° to 149°F (0° to 65°C) | |
| Relative Humidity | 10% to 80% RH, Non-Condensing | |
| BTUs | 17.1 BTU/Hr | |
| FEATURES & SPECIFICATIONS | | |
| USB Specification | USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps) | |
| IP68 Rated | No | |
| IP20 Rated | No | |
| UASP Support | Yes | |
| Driver Required | No | |
| STANDARDS & COMPLIANCE | | |
| Product Compliance | RoHS; CE (Europe); REACH; FCC (USA) | |
| WARRANTY & SUPPORT | | |
| Product Warranty Period (Worldwide) | 3-year limited warranty | |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.