

Universal Reversible USB 2.0 Cable (Reversible A to Reversible A M/M), 3 ft. (0.91 m)

MODEL NUMBER: UR020-003



Reversible USB connector plugs in any direction

Features

- USB 2.0 Male-to-Male, with Universal / Reversible connectors
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold contacts and molded ends provide a lifetime of use

Specifications

OVERVIEW	
UPC Code	037332179388
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	REVERSIBLE USB A (MALE)
Connector Style	Straight
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	3
Cable Length (m)	0.91

Highlights

- 3ft, USB 2.0, Male-to-Male
- Universal, Reversible connector allows plugging in any direction

System Requirements

- Computer with USB A-Female port
- USB device or Patch port with USB A-Female port

Package Includes

- 3ft, USB 2.0, Male-to-Male Universal / Reversible Cable



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Dimensions (hwd / in.)	0.25 x 6.00 x 8.00
Shipping Dimensions (hwd / cm)	0.64 x 15.24 x 20.32
Shipping Weight (lbs.)	0.05
Shipping Weight (kg)	0.02
ENVIRONMENTAL	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.