



# Universal Reversible USB 2.0 Cable (Right / Left-Angle Reversible A to B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR022-006-RA



Reversible Right / Left Angle USB "A" connector plugs in any direction

#### **Features**

- 6ft, USB 2.0 Right / Left Angle A-Male to B-Male, with Universal / Reversible "A" connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

## **Specifications**

| OVERVIEW             |                         |
|----------------------|-------------------------|
| UPC Code             | 037332179470            |
| Technology           | USB 2.0 (High Speed)    |
| Cable Type           | Passive                 |
|                      |                         |
| CONNECTIONS          |                         |
| Side A - Connector 1 | REVERSIBLE USB A (MALE) |
| Side B - Connector 1 | USB B (MALE)            |
| Connector Style      | Angled                  |
|                      |                         |
| PHYSICAL             |                         |
| Cable Jacket Color   | Black                   |
| Cable Length (ft.)   | 6                       |

#### **Highlights**

- 6-ft. (1.83 m), USB 2.0, Right / Left Angle A to B Peripheral device cable
- Universal, Reversible "A" connector allows plugging in any direction

#### **System Requirements**

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

### **Package Includes**

 Universal Reversible USB 2.0 Right / Left Angle A-Male to B-Male Device Cable - 6-ft. (1.83 m)





| 1.83                         |  |
|------------------------------|--|
| 7.00 x 9.00 x 0.50           |  |
| 17.78 x 22.86 x 1.27         |  |
| 0.13                         |  |
| 0.06                         |  |
|                              |  |
|                              |  |
| 14° to 122°F (-10° to 50°C)  |  |
| 5° to 140°F (-15° to 60°C)   |  |
| 0% to 90% RH, Non-Condensing |  |
| 0% to 90% RH, Non-Condensing |  |
|                              |  |
|                              |  |
| RoHS                         |  |
|                              |  |
| WARRANTY & SUPPORT           |  |
| Lifetime limited warranty    |  |
|                              |  |

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.