



Universal Reversible USB 2.0 Extension Cable (Reversible Right/Left-Angle A to A M/F), 6 ft.

MODEL NUMBER: UR024-006-RA



Reversible Right / Left Angle USB "A" connector plugs in any direction

Description

This 6-ft USB extension cable features a Universal / Reversible, Right / Left Angle, A-Male connector, and is manufactured using USB2.0 cable. Universal / Reversible connector allows the cable to be plugged in any direction. This cable is backwards compatible and can also be used with the older USB 1.1 cables. Made with superior foil shielding for reliable error-free data communications. Features nickel plated connectors and gold plated copper contacts for superior conductivity. The cable is manufactured with molded connectors and integral strain relief for extra durability and long life. The significantly faster data transfer rates of USB 2.0 (up to 480 Mbps) makes it perfect for multimedia applications.

Features

- 6ft, USB 2.0 Right / Left Angle A-Male to A-Female Extension, with Universal / Reversible "A" Male connector
- USB 2.0 compliant, to 480Mbps transfer rates
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 28AWG Data Pair, 24AWG Power pair

Specifications

OVERVIEW		
UPC Code	037332179517	
Technology	USB 2.0 (High Speed)	
CONNECTIONS		
Side A - Connector 1	REVERSIBLE USB A (MALE)	

Highlights

- Universal / Reversible A-Male plugs in any direction
- Extend distances of USB 2.0 cables with this extension cable
- Supports faster data transfer rates (1.5 to 480 Mbps) for low speed and high speed devices, especially multimedia applications
- Premium double-shielded cables with tinned copper braid and aluminum mylar foil feature twisted 28/24 AWG data lines
- Gold plated contacts provide superior conductivity

System Requirements

- Any USB device requiring a USB cable
- USB2.0 performance only when used with USB2.0 device and USB2.0 controller

Package Includes

 Universal Reversible USB 2.0 Right / Left Angle A-Male to A-Female Extension Cable - 6ft





Side B - Connector 1	USB A (FEMALE)	
PHYSICAL		
Color	Black	
Cable Length (ft.)	6	
Cable Length (m)	1.83	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.13	
Shipping Weight (kg)	0.06	
ENVIRONMENTAL		
Operating Temperature Range	-10/+75° C (14 to 167° F)	
Storage Temperature Range	-20/+80° C (-4 to 176° F)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks are the property of their respective owners.