



Universal Reversible USB 2.0 Cable (Reversible Right / Left-Angle A to Micro-B M/M), 3 ft. (0.91 m)

MODEL NUMBER: UR050-003-RA



Universal / Reversible "A" connector allows plugging in any direction

Description

The UR050-003-RA USB 2.0 Right / Left Angle A to Micro-B cablefeatures a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Smaller and more durable (10,000 insertion cycles) than the existing mini-B connectors, the Micro-USB will also handle power transfers, as well as data. USB 2.0 rated cable handles 480 Mbps data transfer rates.

Features

- USB Universal / Reversible Right / Left Angle A Male to Micro-B Male, 3-ft. (0.91 m)
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

Specifications

OVERVIEW		
UPC Code	037332179586	
Technology	USB 2.0 (High Speed)	
Cable Type	Passive	
CONNECTIONS		
Side A - Connector 1	REVERSIBLE USB A (MALE)	
Side B - Connector 1	MICRO-USB B (MALE)	
Connector Style	Angled	
Angled Connector	Yes	

Highlights

- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates
- Right / Left Angle, Universal / Reversible "A" Male to Micro-B Male

System Requirements

 Digital devices that use the USB Micro-B Female socket

Package Includes

 3-ft. (0.91 m) USB2.0 Right / Left Angle Universal / Reversible A to Micro-USB B Device Cable (A Male to Micro-B Male)





PHYSICAL		
Cable Jacket Color	Black	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50	
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27	
Shipping Weight (lbs.)	0.11	
Shipping Weight (kg)	0.05	
Unit Dimensions (hwd / in.)	9.000 x 7.000 x 0.500	
ENVIRONMENTAL		
Operating Temperature Range	14° to 122°F (-10° to 50°C)	
Storage Temperature Range	5° to 140°F (-15° to 60°C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
FEATURES & SPECIFICATIONS		
USB Specification	USB 2.0 (up to 480 Mbps)	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

1000 Eaton Boulevard Cleveland, OH 44122 United States https://tripplite.eaton.com © 2024 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.