

Smart 108 SPU - 8-Port Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU22181



Description

Save Space and Money

From SOHO to Enterprise

Features

- 8 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Includes a USB to PS/2 adapter that allows you to use a USB keyboard and mouse on the console end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- 8 Ports
- BIOS level access
- Multilayer security
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cabling
- Includes a USB to PS/2 adapter that allows you to use a USB keyboard and mouse on the console end
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

Operating System

- DOS, Windows, LINUX, UNIX, MAC and all other major operating systems

Console

- VGA Monitor
- USB or PS/2 Keyboard and Mouse

Resolution

- Supports video resolutions up to 1600 x 1200 @ 75Hz

Package Includes

- Smart 108 SPU
- USB to PS/2 Adapter
- RS232 Cable
- Power Cord
- Rackmount Hardware
- Owner's Manual

Specifications

| OVERVIEW | |
|----------|--------------|
| UPC Code | 654518212440 |



Powering Business Worldwide



| | |
|--------------------------------------|----------------------------|
| Console | No |
| CONNECTIONS | |
| Number of Ports | 8 |
| PC/Server Connections | VGA; USB; PS/2 |
| PHYSICAL | |
| Color | Black |
| Shipping Dimensions (hwd / in.) | 7.00 x 7.50 x 1.00 |
| Shipping Dimensions (hwd / cm) | 17.78 x 19.05 x 2.54 |
| Shipping Weight (lbs.) | 3.10 |
| Shipping Weight (kg) | 1.41 |
| Unit Dimensions (hwd / in.) | 1.500 x 8.500 x 4.800 |
| Unit Dimensions (hwd / cm) | 4.15 x 21.5 x 12.2 |
| Unit Weight (lbs.) | 4.1 |
| Unit Weight (kg) | 1.86 |
| ENVIRONMENTAL | |
| Storage Temperature Range | -40 to 70 C / -40 to 158 F |
| Relative Humidity | 80% Non-Condensing |
| Operating Temperature | 0 to 40 C / 32 to 104 F |
| COMMUNICATIONS | |
| Port Control | Push Buttons, Hotkeys, OSD |
| IP Remote Access | Yes |
| FEATURES & SPECIFICATIONS | |
| Number of Users | 1 |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.