

Power-on-Cable (PoC)

MODEL NUMBER: 0SU60020



Description

Completing the OOB Remote Support package

Maximizing power efficiency

Unique "power cord" design

Features

- Seamless integration with KVM and IP devices
- Modular design allows expandability
- 90-260 VAC / 44-66 Hz international coverage
- Current consumption up to 10A
- Flexible power redundancy
- Unique design & 0U footprint
- Easy 3rd party integration with open standard protocol
- Galvanic Separation - no physical connection between management and power device
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Highlights

- Seamless integration with PX and IP Control remote access units
- Modular design allows expandability
- 90-260 VAC / 44-66 Hz international coverage
- Current consumption up to 10A
- Flexible power redundancy
- Unique design & 0U footprint
- Easy 3rd party integration with open standard protocol
- Galvanic Separation - no physical connection between management and power device
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- KVM

Package Includes

- For use with PX (Model #0SU70028) and IP Control (Model #0SU70017) remote access units

Specifications

OVERVIEW	
UPC Code	037332185501



Powering Business Worldwide



Accessory Type	Server Interface Unit
Accessory Class	KVM Switch Accessories
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.60 x 6.60 x 8.80
Shipping Dimensions (hwd / cm)	6.60 x 16.76 x 22.35
Shipping Weight (lbs.)	1.00
Shipping Weight (kg)	0.45
ENVIRONMENTAL	
Storage Temperature Range	-15 to 50 C / 5 to 122 F
Relative Humidity	0 to 95%
Operating Temperature	0 to 50 C / 32 to 122 F
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.