

Smart 116 IP - 16-Port, Remote Access Cat5 KVM Switch for Rack Environments

MODEL NUMBER: 0SU70030



Description

Local or remote access to servers in the data center

Ideal for branch offices and growing companies

Industry standard security

BIOS level, mixed platform access

Features

- 16 Ports
- Remote or Local Access
- BIOS level access
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

Specifications

Highlights

- 16 Ports
- Remote or Local Access
- BIOS level access
- Multi-platform – PS/2 and USB support
- Extends distance between servers and switch up to 30 meters/100 feet over Cat5e cable
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule Purchases

System Requirements

Operating System

- Host & Remote: Windows, Linux

Resolution

- Target Server: 1600 x 1200 @ 85Hz
- Client Computer: Recommended that resolution should be higher than local computer resolution

Package Includes

- Smart 116 IP Cat5 KVM Switch
- RS232 Download Cable
- Rackmount Kit
- Owner's Manual



Powering Business Worldwide



OVERVIEW	
UPC Code	654518209303
Console	No
CONNECTIONS	
Number of Ports	16
PC/Server Connections	VGA; USB; PS/2
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	5.00 x 1.08 x 1.66
Shipping Dimensions (hwd / cm)	12.70 x 2.74 x 4.22
Shipping Weight (lbs.)	7.70
Shipping Weight (kg)	3.49
Unit Dimensions (hwd / in.)	1.600 x 17.000 x 9.100
Unit Dimensions (hwd / cm)	4.1 x 43.1 x 23
Unit Weight (lbs.)	5.6
Unit Weight (kg)	2.54
ENVIRONMENTAL	
Storage Temperature Range	-40 to 70 C / -40 to 158 F
Operating Temperature	0 to 40 C / 32 to 104 F
COMMUNICATIONS	
Port Control	Hotkeys, OSD, Remote Toolbar
IP Remote Access	Yes
FEATURES & SPECIFICATIONS	
NIAP-Certified Secure	No
Number of Users	1
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty