

PX Serial Remote KVM Access

MODEL NUMBER: 0SU70033



Description

Non-blocking serial device access

Complete access to your computer - any time, anywhere

Complete remote support for mission critical applications

Scalable centralized management

Features

- Single port, palm-sized device
- BIOS level access over IP connection
- Management system enabled
- Cost-effective & easily scalable
- Ideal for isolated/widely distributed servers
- Supports data rates from 110 bps to 460.8 Kbps
- Supports ICMP, IP, TCP, UDP, DHCP, BootP, ARP / RARP, DNS, SNMP MIB II, HTTPS, SSH
- Built-in 1.5 KV magnetic isolation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

Highlights

- Single port, palm-sized device
- BIOS level access over IP connection
- Management system enabled
- Cost-effective & easily scalable
- Ideal for isolated/widely distributed servers
- Supports data rates from 110 bps to 460.8 Kbps
- Supports ICMP, IP, TCP, UDP, DHCP, BootP, ARP / RARP, DNS, SNMP MIB II, HTTPS, SSH
- Built-in 1.5 KV magnetic isolation
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

System Requirements

- Supports data rates from 110 bps to 460.8 Kbps
- Supports ICMP, IP, TCP, UDP, DHCP, BootP, ARP / RARP, DNS, SNMP MIB II, HTTPS, SSH

Package Includes

- PX Serial
- Power Supply
- Mounting Kit Footpads
- CD



Powering Business Worldwide



OVERVIEW	
UPC Code	654518209297
Accessory Type	Remote Management
Accessory Class	KVM Switch Accessories
PHYSICAL	
Color	Silver
Shipping Dimensions (hwd / in.)	2.40 x 9.00 x 5.60
Shipping Dimensions (hwd / cm)	6.10 x 22.86 x 14.22
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
ENVIRONMENTAL	
Storage Temperature Range	-20 to 85 C / -4 to 185 F
Relative Humidity	5 to 95% Non-Condensing
Operating Temperature	-10 to 70 C / 14 to 158 F
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.