

PX USB Power Supply 12VDC 1000mA

MODEL NUMBER: 0SU70042



Highlights

- External power supply for the PX USB (0SU70028)
- Provides an alternative to power the PX USB instead of Power Over Ethernet (PoE)
- Input: 100-240V, 50/60Hz, 0.5A
- Output: 12V, 1000mA

System Requirements

- PX USB (0SU70028)

Package Includes

- External Power Supply
- NEMA 1-15P, CEE 7/16 European Plug, BS1363 UK Plug, AS 3112 Australian Plug adapters

Description

The PX USB (0SU70028) remote access unit can be powered using Power Over Ethernet (PoE) or an external power supply. The 0SU70042 external power supply is not included with the PX USB, and is required if Power Over Ethernet (PoE) is not a viable option. It comes with multiple connector types (NEMA 1-15P, CEE 7/16 European Plug, BS1363 UK Plug, AS 3112 Australian Plug), allowing you to use the version appropriate to your power source. Input: 100-240V, 50/60Hz, 0.5A. Output: 12V, 1000mA.

Features

- External power supply for the PX USB (0SU70028)
- Provides an alternative to power the PX USB instead of Power Over Ethernet (PoE)
- Includes multiple connector types (NEMA 1-15P, CEE 7/16 European Plug, BS1363 UK Plug, AS 3112 Australian Plug)
- Input: 100-240V, 50/60Hz, 0.5A
- Output: 12V, 1000mA

Specifications

OVERVIEW	
UPC Code	654518210507
Accessory Type	Power Supply
Accessory Class	KVM Switch Accessories
PHYSICAL	
Shipping Dimensions (hwd / in.)	4.00 x 5.40 x 6.40
Shipping Dimensions (hwd / cm)	10.16 x 13.72 x 16.26
Shipping Weight (lbs.)	0.70



Powering Business Worldwide



Shipping Weight (kg)	0.32
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	6-month limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.